

# SVA ALUMINUM Smoke Vent, Single Leaf

# Application

Acudor Smoke Vents are designed to provide an economical solution for fire ventilation by removing deadly smoke, heat, and gases from a burning building. Single leaf Smoke Vents are used for smaller areas that need venting, including elevator shafts and stairwells. Single leaf units are not U.L. Listed.

## **Features SVA**

- 1/8" thick aluminum
- 12" high insulated curb
- Inside and Outside manual release • High performance gas springs
- UL Listed Fusible or McCabe Resettable Link
- Stainless Steel Hardware

## **Optional Features SVA**

- Curb mount or Metal Building Flange
- Double-Dome Polycarbonate lids for daylighting
- · Louvered curb for ventilation

## **SVA Specifications:**

- Cover: Double-skin construction ("in box type design") with 1" Polyiso (R-6) insulation and a continuous EPDM foam weather/draft seal gasket that is attached to the inside of cover to provide a flush, tight fit. Designed to support a live load of 40lbs./sq. ft., the cover is 1/8" thick aluminum with a 20 gauge aluminum inside liner.
- Curb: 1/8" Aluminum with 1" thick Polyiso (R-6) insulation at curb exterior. Curb is 12" high, with 3.375" wide bottom flange and pre-drilled mounting holes.

Hinge: Aluminum pintle hinges with 3/8" pin

	Curb ID W&L	Weight per Hatch
Model	inches (mm)	lbs. (kg.)
SVA2424	24 x 24 (610 x 610)	60 (27.3)
SVA2436	24 x 36 (610 x 914)	70 (31.8)
SVA3030	30 x 30 (762 x 762)	75 (34.0)
SVA3036	30 x 36 (762 x 914)	85 (38.6)
SVA3096	30 x 96 (762 x 2438)	212 (96.1)
SVA3636	36 x 36 (914 x 914)	95 (43.2)
SVA4848	48 x 48 (1219 x 1219)	123 (55.8)

### **SVA STANDARD SIZES** (other sizes available)

### For detailed specifications see submittal sheet



Opening: Gas spring operators allow cover to open and close with ease. Inside and outside release allows for manual lid operation.

Door Latch: Self latching Slam Latch. Supplied standard with 165° UL Listed Fusible Link. Resettable McCabe link available. Finish: Mill Finish

1/8 (.125) ALUMINUM COVER 1/8 (.125) ALUMINUM COVER 20GA (.032) ALUMINUM COVER LINER 1" POLYISO R6 INSULATION 1/8 (.125) ALUMINUM CURB 3/16 ALUM HINGE BE WITH 3/8 PIN ST/ST MANUAL OUTSIDE RELEASE 1" POLYISO INSULATIO IANUAL INSIDE BELEASE

U.S.A.: info@acudor.com / 800.722.0501 MEXICO: infomx@acudor.com / +521 (844) 101-0081 CANADA: info@acudor.ca / 844.228.3671 INDIA / MIDDLE EAST / NORTH AFRICA: ap-imea@acudor.com / +971-4-399-6966

INTERNATIONAL: info@acudorintl.com / 905.428.2240 SITE: www.acudor.com

This document contains proprietary information which is the property of Acudor Products. It shall not be modified, copied, furnished, nor distributed (in whole or in part) without proper authorization. Copyright 🕲 2020 Acudor Products.