

# AGSAAB Datasheet

Audible Alarm Beacon





# **Product Overview**

Here is a highly effective way to provide a visual and/or audible indication of an alarm. The combination of alarm and super bright flashing LEDs offer excellent protection for an array of circumstances as they draw attention in a hurry. The sirens and strobes will work in conjunction with our Merlin control panels. For other applications contact American Gas Safety for additional technical information.

## **Key Features**

- Alarm/siren offers 32 selectable sounds and volume control.
- Include high intensity LEDs.
- 8 flash patterns.
- Typical working properties of polycarbonate are -40° to 250°F (-40°C to 121°C).
- Three year guarantee against breakage of polycarbonate in normal use (one year on electro mechanical and electronic components).
- Designed to meet the requirements of IP54.

### **Technical Specifications**

General	Installation
Model	AGSAAB
Operating Voltage	12VDC-24VDC
Operating Current	0.42A@12VDC, 0.22A@24VDC
Operating Temperature	-4°F - 140°F
Volume @1 foot	High 105dB, Low 85dB
8 Flash Patterns	Yes
Strobe Speed Control	No
32 Sounds	Yes
Strobe Only Control	Yes
Sound Only Control	Yes
Alarm Trigger	Trigger on power
Lens Tamper	N.C. 12VDC, 50mA Dry Contact
IP Rating	IP54

#### Construction

Durable, polycarbonate construction.

#### Installation

Operating environment temperatures for AGSAAB models -4F to 140F (-20C to 40C).

#### **Electronics**

12-24VDC power supply.

### Options

Available with amber, green, blue, red, white, lens.

#### Find out more

#### American Gas Safety LLC

www.americangassafety.com

Head office: 6304 Benjamin Road, Suite 502, Tampa, FL 33634

Tel: (727) 608-4375 Email: info@americangassafety.com