

# AGSEGOKL Datasheet

Emergency Power Off Push Button With Twist-Reset





\*\*CUSTOM LABEL 'EMERGENCY GAS SHUTOFF'

# Construction

Station housing molded of tough polycarbonate

UL listed to U.S. and Canadian safety standards

# Installation

- 5VA flammability rating on back plate and spacer
- ✓ Typical working properties of polycarbonate are -40° to 250°F (-40° to 121°C)
- ✓ Polycarbonate complies with FDA regulations for food contact applications

# **Specification**

- Two (2) Form "C" contacts, DPDT, rated 10 amps @ 125/250 VAC, 1/2 HP, 6 amps @ 30 VDC.
- ✓ Switch rating 10 amps @ 240 VAC resistive and has a timer range:
  - 2 60 seconds (± 15%).
- Indoor use only. Not recommended for outdoor/water applications.
- ✓ Temperature range of button 15° to 120°F (-9° to +49°C).
- 1 N.O. and 1 N.C. contact.

# **Product Overview**

The AGS-EGOKL, multipurpose push button to be used for a wide range of applications with the AGS Merlin range of gas safety systems.

The AGS-EGOKL is a key re-set, flush mounted button and comes with a clear protective cover to avoid accidental activations.

### **Key Features**

- Protects against vandalism, accidental damage, dust and grime
- Indoor use only
- Twist release reset
- ADA Compliant

Various colors, text & design types available upon request

# **Dimensions**



#### Find out more

#### American Gas Safety LLC

www.americangassafety.com

Head office: 6304 Benjamin Road, Suite 502, Tampa, FL 33634

Tel: (727) 608-4375 Email: info@americangassafety.com