

1 Ear Headset and Microphone



The 1 Ear Headset and Microphone is a monoaural headset with a built-in noise cancelling boom microphone.

The headset is compatible with our Break Out Box [STS-SJB-3.5 or STS-SJB-RJ11] as part of our Window Intercom Systems. It features a flexible microphone, a comfortable adjustable headband, and clear audio reproduction.

### Features

- Supplied with either a 3.55mm or an RJ11 direct plug-in connector
- → Surround Shield<sup>™</sup> noise cancelling microphone
- Acoustic shock protection with Active Protection™ technology
- > 300° adjustable microphone boom
- Supplied with 5.5cm leatherette ear cushion and spare 5.8cm foam ear cushion



#### Applications

For use where one to one communication takes place at a counter, booth or desk in combination with a Contacta Window Intercom System:

- ) Banks
- › Post offices
- > Ticket offices
- > Information centers
- > Airports

## Standards

- > FCC
- > CE
- > RoHS
- > REACH

# contacta

Phone: (616) 392-3400 Email: sales@contactainc.com www.contactainc.com



# Physical Data

Weight 0.1 lbs	Weight
----------------	--------

## **Technical Data**

Con	nection	RJ11 direct plug-in
	Pattern	Electret
	Impedance	Max. 3.9KΩ
Microphone	Sensitivity	-43±3dB at 1kHz
	Frequency Range	100-10kHz
	Operating Temp.	-20°C-+60°C
	Storage Temp.	-40°C-+70°C
Speaker	Pattern	Dynamic moving coil
	Impedance	150Ω / 300Ω
	Sound Pressure	94±3dB / 91±3dB at 1kHz
	Sound Intensity	80mW / 40mW
	Frequency Range	300-3.4 kHz
	Operating Temp.	-20°C-+60°C