

MATERIAL SPECIFICATIONS

DURA-SON 3.5 mm MB

Product	DURA-SON 3.5 mm MB
Thickness	3.5 mm
"R" value	0.32
Mass	40 oz / sq.yd.
Density	22 lbs / cu.ft
Tensile	214. N/5cm.
Content	Minimum 85% recycled rubber bonded with synthetic rubber
Roll size	24 sq.yd.
Roll Weight	60 lbs
Roll Width	54 in.
Roll Length	48. ft.
Roll Diameter	10 in.
Coverage	216 sq.ft.
Acoustical Value	FIIC 69 / ASTM E 1007- Impact Sound Transmission No suspended ceiling
Moisture Protection	3 mil Polyethylene
Water Vapor Transmission Rate	0.0009g / hr. / sq.ft. Or 0.010g / hr. / sq.m. / ASTM E96
Green Quality	CRI Green Label Plus approved
Anti-Microbial	Naturally resists mold, mildew and fungus growth
Radiant Heated Floors	Suitable for radiant heated floor
LEED	Contributes up to 6 Credits
Flamability	PASS Pill Test / ASTM D2859
Application	High Performance Acoustical Underlayment For Laminate and <u>Floating</u> Engineered hardwood floors Residential & Commercial

Dura Undercushions Ltd.

T: (514) 737-6561

(800) 295-4126

F: (514) 342-7940

E: info@dura-undercushions.com

W: www.duracushion.com