



## 255-220-C

Adjustable Upper Guide with Roller Covers, For up to 2%" frames, Galvanized







USE: Guide plate for sliding gates.

TYPE: Gate guide plate with double adjustment.

FIXING: For welding.

MATERIAL: Body in electrogalvanised steel and rollers in nylon.

RECYCLING: Dispose of the body as ferrous material and the rollers as plastic material in accordance with the current laws in the country of installation.

## PARTS SUBJECT TO WEAR: Rollers.

IMPORTANT: The manufacturer reserves the right to modify the characteristics of the product as required without notice. The manufacturer declines any liability for even partial modifications to the product, and the declared performance values are valid only if the installation procedures are carried out by qualified personnel. The roller does not have load-bearing function, in only having to guide the sash vertically during its sliding movement. It must only be able to withstand minor impacts or sudden unbalancing ( wind gusts, light impacts ).

		TI	ECHN <b>I</b> CAL CHARACTER	IST <b>I</b> C:	S	
		255-220			255-350	
WEIGHT OF PART		2,27 Kg			5,58 Kg	
GATE MIN. THICKNESS		35 mm			62 mm	
GATE MAX. THICKNESS		62 mm			85 mm	
MAINTENANCE FREQUENCY						
PR <b>I</b> VATE HOME	COMPANY		WAREHOUSE	CONDOMINIUM <20 UNITS		CONDOMINIUM > 20 UNITS
2 YEARS*	2 YEARS*		2 YEARS*	1 YEAR*		1 YEAR*
Check rollers.						
Check we <b>l</b> ds.						
*The scheme refers to a normal workplace						
	(not	marine o	r particularly aggressi	ve en	vironments).	

Illustrations not to scale and are for reference only. Imperial units shown are for reference only, use millimeters for most accurate sizes.

All pictures, technical drawings and related specifications belong to Fratelli Comunello Spa and they are defended by rules of copyright.

All uses not expressly authorized will be legally prosecuted. Product specifications are subject to change without notice.





## 255-220-C, 256-220 or 256-300

