

## COMBO UNITS



60X63  
HURRICANE COMBO



60X63 COMBO



56X48 COMBO

<b>Ratings</b>	UL-listed, level-1 bullet-resistant glass	UL-listed, level-1 bullet-resistant glass	UL-listed, level-1 bullet-resistant glass
<b>Materials used</b>	14-gauge galvanized steel frame, level-1 bullet-resistant glass	14-gauge galvanized steel frame, level-1 bullet-resistant glass	14-gauge galvanized steel frame, level-1 bullet-resistant glass
<b>Finish options</b>	ASA 70 gray powder coat standard (custom options available at additional cost)	Standard black powder coat (custom finishes at additional cost)	Standard black powder coat (custom finishes at additional cost)
<b>Rough wall opening dimensions</b>	60" W x 63-1/4" H (+0"/-1/8")	60" W x 63-1/4" max H (+1"/-0")	56-1/2" W x 48-1/4" H (+1"/-0")
<b>Viewable area dimensions</b>	56-1/2" W x 44-1/4" H	56-1/2" W x 44-1/4" H	52" W x 29-1/4" H
<b>Overall unit dimensions (I/S = Inside) (O/S = Outside)</b>	I/S = 59-1/2" W x 63" H O/S = 65-5/8" W x 65-3/4" H	I/S = 59-1/2" W x 63" H O/S = 65-5/8" W x 65-3/4" H	I/S = 56" W x 48" H O/S = 62-1/8" W x 50-3/4" H (with trim) O/S = 56" W x 48" H (no trim)
<b>Minimum wall/jamb thickness</b>	Masonry 10-1/4", Metal 8", Wood 8-1/2"	Masonry 10-1/4", Metal 8", Wood 8-1/2"	Masonry 10-1/4", Metal 8", Wood 8-1/2"
<b>Drawer model</b>	Large Electric Hurricane Transaction Drawer	Large Electric Transaction Drawer	Large Electric Transaction Drawer
<b>Power requirements</b>	110/120 VAC, 20 AMP duplex; interior hookup	110/120 VAC, 20 AMP duplex; interior hookup	110/120 VAC, 20 AMP duplex; interior hookup
<b>Counter dimensions</b>	Standard (58-3/4" W x 23-1/2")	Standard 56-15/16" x 23-1/2" countertop with shelves	Standard 53-3/8" x 23-7/16" with shelves
<b>Counter material</b>	Pressed wood/standard black laminate	Pressed wood/standard black laminate	Pressed wood/standard black laminate
<b>Audio included</b>	Exterior audio components (mic, speaker, call button)	Exterior audio components (mic, speaker, call button)	Exterior audio components (mic, speaker, call button)



50X60 COMBO



32X48 COMBO

<b>Ratings</b>	UL-listed, level-1 bullet-resistant glass	UL-listed, level-1 bullet-resistant glass
<b>Materials used</b>	14-gauge galvanized steel frame, level-1 bullet-resistant glass	14-gauge galvanized steel frame, level-1 bullet-resistant glass
<b>Finish options</b>	Standard black powder coat (custom finishes at additional cost)	Standard black powder coat (custom finishes at additional cost)
<b>Rough wall opening dimensions</b>	50-1/4" W x 59-3/4" H (+1"/-0")	32-1/2" W x 48-1/4" H (+1"/-0")
<b>Viewable area dimensions</b>	45-3/4" W x 29-1/4" H	28" W x 29-1/4" H
<b>Overall unit dimensions (I/S = Inside) (O/S = Outside)</b>	I/S = 49-3/4" W x 59-3/8" H O/S = 55-7/8" W x 62-1/8" H	I/S = 32" W x 48" H O/S = 38-1/8" W x 50-3/4" H
<b>Minimum wall/jamb thickness</b>	Masonry 8-3/4", Metal 6-1/2", Wood 7"	Masonry 10-1/4", Metal 8", Wood 8-1/2"
<b>Drawer model</b>	Large Electric Transaction Drawer	Large Electric Transaction Drawer
<b>Power requirements</b>	110/120 VAC, 20 AMP duplex; interior hookup	110/120 VAC, 20 AMP duplex; interior hookup
<b>Counter dimensions</b>	Standard 47-3/16" x 23-7/16"	Standard 29-15/16" x 23-7/16"
<b>Counter material</b>	Pressed wood/standard black laminate	Pressed wood/standard black laminate
<b>Audio included</b>	Exterior audio components (mic, speaker, call button)	Exterior audio components (mic, speaker, call button)

*Some products may be shown with accessories not included with standard offering or pricing.*