## Foundation Vents

Information Sheet



*Quality You Can Trust Since 1886… From North America's Largest Roofing Manufacturer*™



# **Safety Caps For Chimneys**



Safety Caps for chimneys provide protection against dangerous sparks while reducing downdrafts, clogging, soot, and creosote build-up. They also protect against animal and bird infestation, and deflect other debris and rain from entering the chimney. All Master Flow<sup>®</sup> Safety Caps feature:

- Superior Design... Single piece, heavy gauge hood for longer life and less chance for leaks
  Long-Lasting Construction... No rivets or seams to rust or corrode
  Great Looks... Epoxy powder finish provides long lasting protection (note: stainless steel safety cap is unpainted)
  Quick, Easy Installation... Using only a screwdriver
  Appropriate Code Approval... Meets most fire codes



#### STAINLESS STEEL SAFETY CAPS

- 100% stainless steel construction
- Recommended for coastal areas
- and for coal & oil burning furnaces
- 4 year ltd. warranty

Model No.	Fits Flue Tile Outer Dimensions			
CC1313SS	11½" x 11½" – 13½" x 13½"			
LKSS	Leg Kit			

### **Foundation Vents**

#### POWER

- Removes damaging moisture helps prevent structural decay and mold growth
- Fits in traditional foundation vent openings. with simple plug and go operation
- Up to 330 CFM/airflow to eliminate moisture during peak times
- Tested and approved by independent laboratories



#### **BLOCK STYLE**

- · Aluminum vanes; lintel not required
- For block, brick or frame construction
- Recommended for high level ventilation





#### FIXED-SIZE SAFETY CAPS

- Our most popular safety caps fit all standard size chimneys
- 4 year ltd. warranty

Model No.	Fits Flue Tile Outer Dimensions/Shapes (Rectangular/Leg Kit)		
CC99	7½" x 7½" – 9½" x 9½"		
CC913	7½" x 11½" – 9½" x 13½"		
CC1313	11½" x 11½" – 13½" x 13½"		
LKSS	Leg Kit		



#### DJUSTABLE SAFETY CAPS

- Unique adjustable "lock-jaw" bracket mounts cap securely in place
- 4 year ltd. warranty

Model No.	Fits Flue Tile Outer Dimensions
SCCA	8" x 8" thru 13" x 13"
	8" O.D. Round thru 12" O.D. Round

#### AUTOMATIC

- Automatically opens at 70°F, closes at 40°
- Helps prevent foundation decay
- Lowers risk of frozen pipes
- Replaces manual vent
- Snap-in installation
- Saves energy



#### **GRILL STYLE**

 Designed for nailing to floor joists or as a foundation block replacement



### **GRATE STYLE**

- · Positive open/close damper action
- Lintel for foundation block construction
- Lowers risk of frozen pipes
- Saves energy
- Helps prevent foundation decay



#### COVER

 Easy to mount over any 16"x8" foundation vent



FVC168

Model No.	Style	Color	Construction	Description	N.F.V.A. (Sq. In.)
PFV1	Power	Black	Hi-Density Polyethylene	16" x 8" 330CFM 1yr. ltd. warranty	57
FVRABL	Automatic	Black	Hi-Density Polyethylene	16" x 8"	57
<b>500</b>	Grate	Mill	Die-cast aluminum	With lintel & slide action – 16" x 8"	28
BVSII	Block	Mill	Galv. Steel/Alum.	Moveable louvers-15 <sup>3</sup> / <sup>8</sup> × 8 <sup>*</sup> × 2 <sup>3</sup> / <sup>4*</sup> deep	73
LW1	Grill	Mill	Die-cast aluminum	With damper – 16" x 8"	50
LW1L	Grill	Mill	Die-cast aluminum	With 1 <sup>3</sup> / <sub>8</sub> " lintel & damper – 16" x 8"	50
<b>FVC168</b>	Cover	Mill	Aluminum	Cover- Fits most sizes	_