
# Tech Data: European Style



# Options

- 71" door and panel height cannot be modified
- Use Children's or Oversize for other nonstandard dimensions

## European Style

This style is headrail braced with supporting pedestals attached to the panels.

## European Size

Panels and doors are fixed at 71" in height.

#### **Pilasters**

Adjustable support pedestals are affixed to the bottom of the pilasters. Headrail is attached to the pilaster tops and walls to provide partition stability. Shoes are 22 gauge ASTM A-167 stainless steel with satin finish, not less than 3" in height.

## Door Hardware

Hinges are surface mount and strikes/keepers are wraparound style. Slide latches, coat hooks, and bumpers are surface mounted. Door pulls are through bolted. All fasteners are tamper proof.

## **Brackets**

Stirrup-type one ear, two-ear, and u-brackets are provided with theft resistant fasteners.

#### Headrail

Headrail is extruded, clear, anodized aluminum with an anti-grip profile.

#### Considerations

- Wider pilasters will require two pedestals.
- Local building and ADA code should be reviewed for compliance.
- Directional patterns may limit stall depth.

#### 4/11/2014

Ironwood Manufacturing reserves the right to make changes in design, material, and documentation without formal notice and without incurring obligation. Consult local and national codes: conformity and compliance to local and national codes is the responsibility of the installer. Verify all roughin dimensions prior to installation.