Tech Data: Louvers

Options

Louvers

- Traditional louver widths
- Plantation louver widths

• Mid-stile or mid-rail

Doors and Panels

Louvered doors and panels are built with stile and rail construction, using solid wood or wood veneer with an MDF core. Louvered doors and louvered panels are 1.25" thick.

Pilasters

Shoes are 22 gauge ASTM A-167 stainless steel with satin finish, not less than 3" in height.

Door Hardware

Hinges are surface mount and strikes/keepers are wraparound style. Slide latches, coat hooks, and bumpers are surface mounted. Door pulls are through bolted. All fasteners are tamper proof.

Brackets

Stirrup-type one ear, two-ear, and u-brackets are provided with theft resistant fasteners.

Considerations

- Slats longer than 28" are not recommended without a mid-stile.
- Value engineering options include veneer doors with laminate panels and pilasters.
- Variances between wood and laminate finishes are expected.
- Slats may require additional cleaning care.
- Louvered doors are not guaranteed in wet areas.

4/11/2014

Ironwood Manufacturing reserves the right to make changes in design, material, and documentation without formal notice and without incurring obligation. Consult local and national codes: conformity and compliance to local and national codes is the responsibility of the installer. Verify all roughin dimensions prior to installation.