

Product Data

VIPERVENT® CDR

Complete Drained Roof



Description

ViperVent® CDR is a 0.30-inch, randomly oriented, geometric patterned drainage and ventilation mat.

The product is designed to eliminate moisture and moisture vapor in cedar roofing, siding applications, and metal roofing applications.

ViperVent® CDR is produced from an extruded polymer matrix of tangled monofilaments, which are heat-welded at the junctions to form a structure that spaces siding and roofing away from the inner sheathing.

The product is useful in cedar and metal roofing and siding applications in which a clean airspace is desired for ventilation and drainage.

Applications

- ✓ Roofing applications including cedar shingles and shakes
- ✓ Metal roofing applications
- ✓ Zinc roofing applications
- ✓ Siding applications
- ✓ Asphalt shingles
- ✓ Fiberglass Shingles
- ✓ SIP Roofs
- ✓ Other roofing applications*

For Installation Instructions please see document: KC-02002

** For more information on roofing applications, please contact our office at 877-514-5336*

Features and Benefits

Drainage of excess moisture and ventilation in one product

Lightweight and easy to handle

Simple installation with mechanical staple hammer

Polymer core resistant to most known corrosive chemicals, including solvents

Wide rolls for fewer seams

Core absorbs and releases no moisture

Provides no source for the promotion of MOLD, MILDEW or BACTERIA

Physical Properties

Description		Measurement	
Flame Spread		ASTM E84	Class A
Core Polymer		Polymeric	
Thickness	(01-X-0006)	0.30 in.	7.6 mm
	(01-X-0007)	0.30 in.	7.6 mm
	(01-X-0156)	0.40 in.	10.1 mm
Weight of Core	(01-X-0006)	1.25 oz/ft ²	
	(01-X-0007)	1.25 oz/ft ²	
	(01-X-0156)	1.40 oz/ft ²	

Packaging

Product Name	Product Part Number	Rolls per Unit	Units per Truck	Weight per Roll		Length per Roll		Coverage	
				lb	kg	ft	m	sq ft	sq m
ViperVent® CDR	01-X-0006	18	26	18.75	8.5	60	18.3	240	22.3
ViperVent® CDR	01-X-0007	18	26	15.65	7.1	50	15.3	200	18.6
DW CEDAIR VENT	01-X-0156	18	26	17.5	7.9	50	15.3	200	18.6

LIMITED WARRANTY: Keene Building Products, Inc. ("Keene") warrants its VIPER VENT products against defects in material and workmanship for a period of Twenty-Five (25) years from the date of installation. Upon receipt of written notice, which must be given no later than thirty (30) days after discovery of the defect, Keene, at its sole option, will repair or replace the defective item(s) or refund the purchase price. Keene, at its sole option, may request that the defective item(s) be returned to Keene's principal offices for investigation and inspection. Keene is not required to repair or replace the defective item(s) or to refund the purchase price until it has received such item(s) that Keene has requested returned and has inspected such item(s).

The warranty provided above is extended solely to the person or entity that purchases the product directly from Keene, and no third party may rely thereon or assert any claim based on such warranty. The foregoing warranty is the only warranty provided by Keene and is to the exclusion of any other warranty, whether express or implied, including the implied warranties of merchantability and fitness for a particular purpose, all of which are expressly disclaimed. Keene's liability, if any, for damages based on any claim of any kind whatsoever, and regardless of the legal theory, with regard to any of its products shall be limited to the actual purchase price of the product(s) with respect to which such claim is made.

UNDER NO CIRCUMSTANCES SHALL KEENE BE LIABLE TO PURCHASER FOR COMPENSATION, REIMBURSEMENT OR DAMAGES ON ACCOUNT OF THE LOSS OF PRESENT OR PROSPECTIVE PROFITS OR REVENUE, EXPENDITURES, INVESTMENTS OR COMMITMENTS, AND IN NO EVENT SHALL KEENE BE LIABLE TO PURCHASER OR ANY OTHER PERSON OR ENTITY FOR SPECIAL, INCIDENTAL, INDIRECT, CONSEQUENTIAL OR EXEMPLARY DAMAGES. By way of example only, Keene will not be responsible for any damages purchaser may incur that are related to surface, subsurface or building conditions, damage to the structure or contents of any building, or for costs of repair and replacement except as may be expressly provided in this Limited Warranty (and subject to the terms and conditions hereof).

Keene shall not be liable for product failure resulting from any of the following: (i) products not installed in accordance with Keene's installation instructions; (ii) non-compliance with applicable building codes and regulations; (iii) the use of any of its products (A) in a manner for which it was not intended; (B) in a modified form without the permission of Keene, or (C) in combination with any other system, equipment or device not manufactured or sold by Keene.

Keene may change, modify, amend, replace or discontinue offering a product warranty, limited or otherwise. Any such change, modification, amendment, replacement or discontinuance shall be applicable to unsold products only, and Keene shall endeavor to give purchaser at least thirty (30) days prior written notice of same.

Claims or inquiries shall be addressed as follows:

Customer Service Department [Quality Control Manager]

KEENE BUILDING PRODUCTS, INC.

2926 Chester Ave.

Cleveland, OH 44114

P 440 605 1020 [877-514-5336]

F 440 605 1120

www.keenebuilding.com

Document: KC-02002



877 | 514 | 5336
 Info@KeeneBuilding.com P 440 | 605 | 1020 5/7/2024
 KeeneBuilding.com F 440 | 605 | 1120 page 2/2