



Power Stringers

KH PowerTuff temporary stringers are industrial grade and designed to comply with OSHA and NEC regulations for safe, portable power.



Model: PS8DD6-520-B10M-L2120D



Model: PS8DD3-520-B12G-520F

APPLICATIONS

- Manufacturing environments
- Convention centers
- Maintenance repair & operations
- Temporary & emergency shelters

FEATURES

- Length: 30' or 60' is standard; custom lengths available
- 15 or 20 Amps, single or 3-phase
- Electrical box: Heavy duty rubber outlet box in low contrast black
- Cord: 12 or 10 AWG 600 VAC, SOOW cable
- Color coded receptacles for easy phase identification
- Receptacles: Duplex is standard
- Components meet CSA/UL standards
- Indoor NEMA rating
- Also available with weather resistant duplex, single 1.39, single 1.56, weather resistant GFCI and blank coverplates
- Made from non-metallic and non-conductive materials to protect against electrical shock

OPTIONS

- Feed through or dead end
- Custom configurations available
- Can place the outlet boxes at any point on the stringer

Temporary power stringers available in feed through and dead end.



Length: 30'

Model No.	Output	# of Boxes	VAC	# of Poles	# of Wires	AWG	NEMA Receptacle	NEMA Inlet	NEMA Outlet	Spacing	Phase
PS8DD3-520-B12G-520D	Dead End, Extra Depth	3	125	2	3	12	(6) 5-20R	Straight Blade 5-20P	N/A	10-10-10	Single
PS8DD3-520-B12G-520F	Feed Through, Extra Depth	3					(6) 5-20R		Straight Blade 5-20C	7-10-10-3	Single
PS8DD2-520-B12G-L1420D	Dead End, Extra Depth	2	125/250	3	4		(4) 5-20R	Locking Blade L14-20P	N/A	15-15	Single
PS8DD2-520-B12G-L1420F	Feed Through, Extra Depth	2					(4) 5-20R		Locking Blade L14-20C	12-15-3	Single
PS8DD3-520-B10G-L2120D	Dead End, Extra Depth	3	120/208	4	5	10	(6) 5-20R	Locking Blade L2120-P	N/A	10-10-10	Three
PS8DD3-520-B10G-L2120F	Feed Through, Extra Depth	3					(6) 5-20R		Locking Blade L2120-C	7-10-10-3	Three

Length: 60'

Model No.	Type	# of Boxes	VAC	# of Poles	# of Wires	AWG	NEMA Receptacle	NEMA Inlet	NEMA Outlet	Spacing	Phase
PS8DD4-520-B12M-L1420D	Dead End, Extra Depth	4	125/250	3	4	12	(8) 5-20R	Locking Blade L14-20P	N/A	15-15-15-15	Single
PS8DD4-520-B12M-L1420F	Feed Through, Extra Depth	4					(8) 5-20R		Locking Blade L14-20C	12-15-15-15-3	Single
PS8DD6-520-B10M-L2120D	Dead End, Extra Depth	6	120/208	4	5	10	(12) 5-20R	Locking Blade L21-20P	N/A	10-10-10-10-10-10	Three
PS8DD6-520-B10M-L2120F	Feed Through, Extra Depth	6					(12) 5-20R		Locking Blade L2120-C	7-10-10-10-10-3	Three

Contact a sales rep for additional info about a specific model number. Custom configurations available.



Locking blade shown

