Quad Lights Portable Lighting Systems

Temporary and portable wide area lighting for demanding work environments.

4 Foot High: LED: 80 Watts/7,200 Lumens Fluorescent: 128 Watts/ 11,800 Lumens

Model: QL410C-16A-10A

2 Foot High: LED: 40 Watts/5,000 Lumens Fluorescent: 68 Watts/5,200 Lumens

APPLICATIONS

Manufacturing, Inspection and Maintenence in:

- Aircraft
- Ground Transportation
- Marine and Ship Building
- Temporary Emergency Shelters/Tents

FEATURES

- Protected on/off switch
- User serviceable replacement parts, with most parts interchangeable between the two Quad Light sizes
- Integrated covered outlets allow feed through lighting
- Power Cord: 14/3 SJOW black; oil and water resistant
- Attachment Plug and Outlets: NEMA 5-15 for daisy chain, feed through lighting and grounded plug and connector
- String up to 12 fluorescent and 20 LED Quad Lights
- Durable design for rough service areas and continual use, includes lamp shock absorbers and impact resistant bulbs that protect against breakage from accidental drops and falls.
- Custom configurations available

SPECIFICATIONS

- 4 Foot Model
- LED: 80 Watts/7,200 Lumens
- Fluorescent: 128 Watts/11,800 Lumens
- 2 Foot Model
- LED: 40 Watts/5,000 Lumens
- Fluorescent: 68 Watts/5,200 Lumens



The Permanent Name in Temporary Lighting & Power Durable design resists breakage -LED or fluorescent bulbs available!



Model: QL420C-16A-10A

Quad Lights - 2 Foot Model

2 Foot Model (actual dimensions are: 27.75″L x 7.25″W x 5.75″D) LED: 40 Watts/5,000 Lumens Fluorescent: 68 Watts/5,200 Lumens						
Model No.	Lamp Туре	Watts	Cord Length	Special Operation		
QL410C-16A-10A	LED	40	10′	N/A		
QL410C-16A-25A			25′			
QL410C-16F-10A			10′	Battery Back Up*		
QL417R-16E-10	Fluorescent	68	10′	N1/A		
QL417R-16E-25			25′	N/A		

Quad Lights - 4 Foot Model

4 Foot Model (actual dimensions are: 52"L x 7.25"W x 5.75"D) LED: 80 Watts/7,200 Lumens Fluorescent: 128 Watts/11,800 Lumens						
Model No.	Lamp Туре	Watts	Cord Length	Special Operation		
QL420C-16A-10A	LED	80	10′	N/A		
QL420C-16A-25A			25′			
QL420C-16F-10A			10′	Battery Back Up*		
QL432R-16E-10	Fluorescent	128	10′	N/A		
QL432R-16E-25			25′			

* Battery back-up model features an auxiliary LED strip that automatically turns on when 120 VAC power service is interrupted.





