

# 1" BLINDS + GLASS XL FOR WINDOWS & SLIDING PATIO DOORS

Constant was

#### **PRODUCT FEATURES**

- Use in large format sliding patio doors and windows for residential and light commercial applications
- Effortless raise, lower and tilt function available in left-hand or right-hand EasyGlide operator
- Easy to maintain, simply clean with soap and water, or high quality window cleaner
- 10-year full warranty
- Blinds certified safe for children and pets with no exposed cords





SIZES	
IG Thickness	ן"
Height Range	46" to 90"
Width Range	9" to 63"
Size Increments	1/16" (height & width)
Max IG size	Tempered Only, Max area: 28 sq. ft., no more than 48" in 1 direction

Please refer to charts located on the right for custom size options.

LOW-E OPTIONS		
Single	270, 272, 340 and 366	
Dual	189/270, 189/272, 189/340, & 189/366	

#### **FINISH OPTIONS**

Blind slats, operators, operator track and decorative cover caps are available in six different colors



ESPRESSO SAND





MOON








TAN WHITE






1.866.472.0042 | odl.com/blinds U.S. Patent Pending




## 1" BLINDS + GLASS XL FOR WINDOWS & SLIDING PATIO DOORS

### TECHNICAL DRAWINGS & SPECIFICATIONS



OPERATION	
Blind Function	Raise, Lower, and Tilt
EasyGlide Operator	Clear Overmold/Two Shot
<b>Dual Operator</b>	Tempered glass: Up to 28 sq ft
<b>Dual Operator</b>	See size chart for details
Capillary Tube	Do not block, crush or cut
Operator Hand	Left or right

CODE OF COMPLIANCE		
IGCC (seal)	ASTM E2190 seal certification	
ANSI (glass)	ANSI Z97.1 safety glazing (Applies to tempered glass only)	
ASTM (glass)	C1048-12 (tempered)	
ANSI (safety)	ANSI / WCMA A100.1-2018	
ENERGY STAR®	Will help your window achieve ENERGY STAR® performance when select Low-E glass is employed	
NFRC	CAD available for simulations	



MATERIALS	
Spacer	Intercept®, tin plated steel
Glass (Standard or Low-E)	4mm tempered safety glass
Single Low-E	2nd surface soft coat (270, 272, 340, 366)
Dual Low-E	4th surface hard coat Low-E (189)
Blind Slat	10mm wide aluminum UV stabilized coating
Sealant	Dual seal equivalent
Desiccant	Desiccant matrix (moisture & chemical management)
Decorative Cover Caps	UV stabilized, heat tolerant polymer