

PRODUCT FEATURES

- For use in single and double-hung windows
- Easy raise, lower, and tilt operation
- Streamlined EasyGlide Operator and Ergo Track located on top center
- Easy to maintain, simply clean with soap and water, or high quality window cleaner
- 10-year full warranty
- Blinds certified safe for children and pets with no exposed cords





7/8"
12" to 41"
15" to 54"
1/16" (height & width)
Annealed glass: Up to 9 sq. ft. Tempered glass: Up to 9 sq. ft. (no more than 36" in one direction)

Please refer to charts located on the right for custom size options.

LOW-E OPTIONS		
Single	270, 272, 340 and 366	
Dual	189/270, 189/272, 189/340, & 189/366	

GLASS TINT OPTIONS

Solar Gray

Solar Bronze

FINISH OPTIONS

Blind slats, operators, operator track and decorative cover caps are available in six different colors





CUSTOM SIZE OPTIONS



Annealed and Tempered

SINGLE OPERATOR

Max IG Size: 9 sq. ft. (no more than 36" in one direction) Operator location top center

TECHNICAL DRAWINGS & SPECIFICATIONS

.875 (min .855 not to exceed .910)



Sealant Over Capillary Texeed. 125 For Edge of Glass DETAIL A Edge of Glass <p< td=""><td>Image: constraint of the sector o</td></p<>	Image: constraint of the sector o

OPERATION		
Blind Function	Raise, Lower, and Tilt	
EasyGlide Operator	Clear Overmold/Two Shot	
Single Operator	Annealed glass: Up to 9 sq. ft. or Tempered glass: Up to 9 sq. ft.	
Capillary Tube	Do not block, crush or cut	
Operator Hand	Top Center	

CODE OF COMPLIANCE		
IGCC (seal)	ASTM E2190 seal certification	
ANSI (glass)	ANSI Z97.1 safety glazing (Applies to tempered glass only)	
ASTM (glass)	ASTM C1036-16 (annealed) & C1048-12 (tempered)	
ANSI (safety)	ANSI / WCMA A100.1-2018	
ENERGY STAR®	Will help your window achieve ENERGY STAR® performance when select Low-E glass is employed	
NFRC	CAD available for simulations	

MATERIALS	
Spacer	Intercept®, tin plated steel
Glass (Standard or Low-E)	1/8" annealed or 1/8" tempered safety glass
Single Low-E	2nd surface soft coat (270, 272, 340, 366)
Dual Low-E	4th surface hard coat Low-E (189)
Glass Tint	Solar Gray or Solar Bronze: glass panel 1
Blind Slat	10.5mm wide aluminum UV stabilized coating
Sealant	Dual seal equivalent
Desiccant	Desiccant matrix (moisture & chemical management)
Decorative Cover Caps	UV stabilized, heat tolerant polymer

U.S. Patent No. 10,876,353 B2 223556 (12/23)



