

VERTICAL GRATING OMEGA 100

ZINC COATING
STEEL



OMEGA 100

Design	Sunscreen shades (100% view blocking)
Vertical wires	Round, 8 GA (Diameter 4 mm)
Wires spacing	5 3/16" (132 mm)
Louver	Flat (2 3/4" x 1/16" / 69mm x 1.59 mm)
Louver Spacing	1 3/4" (46 mm)
Standard Height	77.75" (1975 mm)
Standard Length	65" (1650 mm)
Gap Bottom panel/Ground	1 3/16" (30 mm)
Bolting	Carriage Bolt 5/16" (8 mm) - Standard nuts or Tamper Proof
Post options	Flat / Flanged - Square / Flanged
Cap options	Flat post = no cap, Square post = Square cap
SPF (Special Panel Fitting)	Side Fitting
Opacity/Openness	100% / 0%

