



VERTICAL GRATING OMEGA 80



ZINC COATING
STEEL



OMEGA 80

Design	Sunscreen shades (80% view blocking)
Vertical wires	Round, 8 GA (Diameter 4 mm)
Vertical wires spacing	5 3/16" (132 mm)
Louver	Flat (2" x 1/16" / 50mm x 1.59mm)
Louver Spacing	1 3/4" (46 mm)
Standard Height	77.5" (1963mm)
Standard Length	65" (1650 mm)
Gap Bottom panel/Ground	1 3/16" (30 mm)
Bolting	Carriage Bolt 5/16" (8 mm) - Standard nuts or Tamper Proof
Post options	Flat / Flanged - Square / Flanged
Cap options	Flat post = no cap, Square post = Square cap
SPF (Special Panel Fitting)	Side Fitting
Opacity/Openness	92.5% / 7.5%

