



Directory Search

[New Search](#)

NFRC Codes

[Exit Directory Search](#)

Detailed Product Ratings

GENERAL INFORMATION	
Manufacturer:	Paradigm Window Solutions
Series Name:	8331 Hopper Window
Operator Type:	PRAW
Air Leakage:	
Ventilation Rating (Standard Screen):	
Ventilation Rating (Enhanced Screen):	

RATINGS INFORMATION

(Found 95 Products)

[Request Export](#)
[<< First](#)
[< Previous](#)
[Next >](#)
[Last >>](#)

CPD #	Manufacturer Product Code	U-factor	SHGC	VT	Condensation Index	Product Description
PWS-A-9-00673-00001	No Foam / No Reinforcement: CLR / Air / CLR (DS-DS) 3/4"	0.42	0.54	0.56	56	Vinyl/Vinyl, Fill 1: AIR (100), CL, No Grid
PWS-A-9-00673-00002	No Foam / No Reinforcement: CLR / Air / CLR (DS-DS) 3/4"	0.42	0.44	0.46	56	Vinyl/Vinyl, Fill 1: AIR (100), CL, Grid
PWS-A-9-00674-00001	No Foam / No Reinforcement: CLR / Air / CLR (DS-DS) 3/4"	0.42	0.49	0.51	56	Vinyl/Vinyl, Fill 1: AIR (100), CL, Grid
PWS-A-9-00675-00001	No Foam / No Reinforcement: LoE 270 / Arg / CLR (DS-DS) 3/4"	0.26	0.26	0.48	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
PWS-A-9-00675-00002	No Foam / No Reinforcement: LoE 270 / Arg / CLR (DS-DS) 3/4"	0.26	0.21	0.39	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00676-00001	No Foam / No Reinforcement: LoE 270 / Arg / CLR (DS-DS) 3/4"	0.26	0.23	0.43	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00677-00001	No Foam / No Reinforcement: CLR / Arg / LoE 270 (DS-DS) 3/4"	0.26	0.32	0.48	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
PWS-A-9-00677-00002	No Foam / No Reinforcement: CLR / Arg / LoE 270 (DS-DS) 3/4"	0.26	0.26	0.39	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00678-00001	No Foam / No Reinforcement: CLR / Arg / LoE 270 (DS-DS) 3/4"	0.26	0.29	0.43	67	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00679-00001	No Foam / No Reinforcement: LoE 270 / Arg / i89 (DS-DS) 3/4"	0.23	0.25	0.47	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid

PWS-A-9-00679-00002	No Foam / No Reinforcement: LoE 270 / Arg / i89 (DS-DS) 3/4"	0.23	0.21	0.38	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00680-00001	No Foam / No Reinforcement: LoE 270 / Arg / i89 (DS-DS) 3/4"	0.23	0.23	0.42	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00681-00001	No Foam / No Reinforcement: LoE 180 / Arg / i89 (DS-DS) 3/4"	0.23	0.43	0.53	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
PWS-A-9-00681-00002	No Foam / No Reinforcement: LoE 180 / Arg / i89 (DS-DS) 3/4"	0.23	0.35	0.43	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00682-00001	No Foam / No Reinforcement: LoE 180 / Arg / i89 (DS-DS) 3/4"	0.23	0.39	0.48	61	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00683-00001	No Foam / No Reinforcement: CLR / Air / CLR (5MM-5MM) 3/4"	0.43	0.52	0.55	56	Vinyl/Vinyl, Fill 1: AIR (100), CL, No Grid
PWS-A-9-00684-00001	No Foam / No Reinforcement: CLR / Air / CLR (5MM-5MM) 3/4"	0.44	0.42	0.45	51	Vinyl/Vinyl, Fill 1: AIR (100), CL, Grid
PWS-A-9-00684-00002	No Foam / No Reinforcement: CLR / Air / CLR (5MM-5MM) 3/4"	0.44	0.47	0.50	51	Vinyl/Vinyl, Fill 1: AIR (100), CL, Grid
PWS-A-9-00685-00001	No Foam / No Reinforcement: LoE 270 / Arg / CLR (5MM-5MM) 3/4"	0.27	0.25	0.47	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
PWS-A-9-00686-00001	No Foam / No Reinforcement: LoE 270 / Arg / CLR (5MM-5MM) 3/4"	0.29	0.21	0.38	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00686-00002	No Foam / No Reinforcement: LoE 270 / Arg / CLR (5MM-5MM) 3/4"	0.29	0.23	0.42	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00687-00001	No Foam / No Reinforcement: CLR / Arg / LoE 270 (5MM-5MM) 3/4"	0.27	0.31	0.47	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
PWS-A-9-00688-00001	No Foam / No Reinforcement: CLR / Arg / LoE 270 (5MM-5MM) 3/4"	0.29	0.26	0.38	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00688-00002	No Foam / No Reinforcement: CLR / Arg / LoE 270 (5MM-5MM) 3/4"	0.29	0.29	0.42	68	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, Grid
PWS-A-9-00689-00001	No Foam / No Reinforcement: LoE 270 / Arg / i89 (5MM-5MM) 3/4"	0.24	0.25	0.46	64	Vinyl/Vinyl, Fill 1: ARG (90), LowE, CL, No Grid
1 2 3 4						

Key:

Click the column headers to sort the data according to the column header.

A dash "-" in a rating column (SHGC / VT) indicates that there are no NFRC certified values for that individual product.

Copyright © 2025 National Fenestration Rating Council Incorporated ("NFRC") All rights reserved. NFRC's CMA data is protected by copyright. By accessing and downloading NFRC data from this webpage, the user agrees to abide by the [Terms of Use](#).

The website is optimized for current browsers.

DISCLAIMER OF LIABILITY:

In no event shall the NFRC be liable for any damages whatsoever (including, without limitation, damages for loss of business profits, business interruption, loss of business information, or any other loss) arising out of the use of this website or the information obtained from it, whether incidental or consequential. This provision shall apply even if the NFRC has been advised of the possibility of such damages.