



pushbuttonreader

DATA SHEET

Push Button Reader

The Push Button Reader equipped with a rugged backlit keypad, weatherproof design, and a durable zinc alloy casing, is built for applications where durability is key. The Push Button Reader offers the ability to unlock doors with proximity credentials, PIN, or the flexibility to configure two-layer security by requiring users to present a credential and enter a PIN to gain access.

Model

PN: RDRPB

Specifications:

Input

Frequency: 125 KHZ

Read Range: from 1.1" up to 2.3"

Output

Wiegand protocol

Cable Distance: Wiegand 500' (22 AWG)

Environmental

Temperature: -40° ~ +140° F or -40° ~ +60° C

Humidity: 0 - 95% relative humidity, non-condensing

Protection Rating: IP65

Enclosure

Dimensions: (W x H x D) 3.22" x 5.03" x 1.10"

Weight: 1.43 lbs / 22.9 oz / 650 g

Power

12-18V AC/12-24V DC (Linear power supply recommended)

Manufacturer's Limited Warranty

One to five-year warranty against defects in materials and workmanship. For full details, visit www.prodatakey.com/warranty



Visit www.prodatakey.com/resources to access marketing, installation, and support resources. For questions about the PDK Push Button Reader, please contact support@prodatakey.com.