



# PLD18S1 TECHNICAL SPECIFICATION

Job Name _____	Item # _____
Location _____	
Engineer _____	Contractor _____
PO # _____	Tag _____
Representative _____	

## DESCRIPTION

- Sink Drain
- 18 Gauge 316L Stainless Steel
- Key feature of the drain body is a fully-sloped trough that prevents standing water and solids being deposited into the trough
- 1.5" I.D. schedule 10 stainless steel waste outlet
- NOT SUITABLE AS A FLOOR DRAIN
- Height adjustability of drain cover with use of spacers for different thicknesses of finished material from 3/8" to 3/4". Custom spacers are available for finished material thicknesses from 1"-2 1/2"
- QuickDrain USA recommends the drain cover extend the entire length of the sink

## DRAIN BODY INCLUDES

- Height Adjustable Spacers (2)


## REQUIRED PART (NOT INCLUDED) - DRAIN COVER

- Available in the designs below and in this length – 18"


## APPROVALS AND LISTINGS

Before installing QuickDrain USA system, check with your local building department/plumbing inspector to ensure compliance with the local building codes. QuickDrain USA LLC is not responsible for any conflicts with local building codes. QuickDrain USA LLC is not responsible for improper installation of any part of the assembly or the waterproofing membrane. Dimensions are subject to manufacturer's tolerance and can change without notice.


MODEL NUMBER	HEIGHT ADJUSTABLE SPACERS	COVER LENGTH
PLD18S1	2	COVER18




Cosmo




Horizontal\*




Vertical\*



TileIn\*




Lines




Stream

## PROLINE SINK DRAIN ASSEMBLY





# PLD18S1 TECHNICAL SPECIFICATION



MODEL	A	B	C	D
PLD18S1	18	9	9	20

## INSTALLATION NOTES

- Install product according to the Typical ProLine Drain Installation details
- Drain body cannot be cut to size or modified on site