

	PLATFORM TRUCK		CONVERTIBLE PLATFORM TRUCK		WORK-HEIGHT PLATFORM TRUCK		SIDE PANEL TRUCK		SHEET & PANEL	
										
	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>
<b>SMALL</b>	1,000-2,000 LBS.	36" (L) X 24" (W)	–	–	2,000 LBS.	40.1" (L) X 24.25" (W) X 38.9" (H)	1,000-1,200 LBS.	44" (L) X 24.25" (W) X 39.24" OR 41.5" (H)	2,000 LBS.	38.75" (L) X 24.25" (W) X 38" (H)
<b>MEDIUM</b>	1,200-2,500 LBS.	48" (L) X 24" (W)	750 LBS. AS CART 1,000 LBS. AS PLATFORM	61.5" (L) X 24.25" (W) X 41.1" (H)	2,000 LBS.	52.1" (L) X 24.25" (W) X 40.9" (H)	2,000 LBS.	56" (L) X 24.25" (W) X 41.25" (H)	2,000 LBS.	47.9" (L) X 24.25" (W) X 39.9" (H)
<b>LARGE</b>	1,200-2,500 LBS.	60" (L) X 30" (W)	750 LBS. AS CART 1,000 LBS. AS PLATFORM	61.5" (L) X 24.25" (W) X 44.6" (H)	2,000 LBS.	64.1" (L) X 30.25" (W) X 40.75" (H)	1,200-2,000 LBS.	68.1" (L) X 30.25" (W) X 41.4" (H)	2,000 LBS.	59.9" (L) X 30.25" (W) X 39.9" (H)
<b>EXTRA-LARGE</b>	1,000-2,000 LBS.	70" (L) X 40" (W)	–	–	–	–	–	–	–	–
<b>WHEN TO USE</b>	IDEAL FOR TRANSPORTING A WIDE VARIETY OF BULK GOODS, SUPPLIES, AND MATERIALS EFFICIENTLY THROUGHOUT A FACILITY		VERSATILE SOLUTION THAT CAN BE CUSTOMIZED FROM JOB-TO-JOB TO ELIMINATE THE NEED FOR MULTIPLE TRUCKS TO SAVE MONEY & IMPROVE PRODUCTIVITY		ERGONOMIC HEIGHT PLATFORM TRUCKS IDEAL FOR PULLING STOCK, ASSEMBLY OPERATIONS AND OTHER HEAVY TASKS		IDEAL FOR TRANSPORTING AND RETAINING SMALL PACKAGES AND MATERIALS.		IDEAL FOR MOVING BULKY, HARD-TO-HANDLE ITEMS SUCH AS: SHEET GOODS, DOORS, LUMBER, TABLES, AND MATTRESSES	
<b>MATERIAL</b>	HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)	
<b>CASTER &amp; SIZE OPTIONS</b>	TPR: 6" OR 8" POLYOLEFIN: 6" OR 8" PNEUMATIC: 8"		TPR: 6" ON MEDIUM PNEUMATIC: 8" ON LARGE		TPR: 6" ON SMALL, 8" ON MEDIUM AND LARGE		TPR: 6" OR 8" PNEUMATIC: 8"		POLYOLEFIN: 6" ON SMALL, 8" ON MEDIUM AND LARGE	
<b>COLOR</b>	BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED	
<b>POWDER-COATED METAL</b>	•		•		•		•		•	
<b>HANDLE RETAINER CLIPS</b>	•		•		•		•		•	
<b>TEXTURED DECK SURFACE</b>	•		•		•		•		•	
<b>MOLDED-IN TIE DOWN SLOTS (4)</b>	•		•		•		•		•	

	A-FRAME		CONVERTIBLE A-FRAME		5TH WHEEL WAGON		STANCHION PLATFORM TRUCKS		SEMI-LIVE SKIDS	
										
	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>	<b>WEIGHT CAPACITY</b>	<b>DIMENSIONS</b>
<b>SMALL</b>	2,000 LBS.	35.9" (L) X 24.25" (W) X 43" (H)	–	–	1,200 LBS.	45" (L) X 24.25" (W) X 16.75" (H)	2,500 LBS.	35.9" (L) X 24.25" (W) X 38.9" (H)	2,000 LBS.	35.9" (L) X 24.25" (W) X 12.5" (H)
<b>MEDIUM</b>	2,000 LBS.	47.9" (L) X 24.25" (W) X 44.9" (H)	–	–	2,000 LBS.	56.25" (L) X 24.25" (W) X 17.5" (H)	2,500 LBS.	47.9" (L) X 24.25" (W) X 42.5" (H)	2,000 LBS.	47.9" (L) X 24.25" (W) X 12.5" (H)
<b>LARGE</b>	2,000 LBS.	59.9" (L) X 30.25" (W) X 44.9" (H)	2,000 LBS.	51.13" (L) X 28.13" (W) X 17.25" (H)	2,000 LBS.	70.1" (L) X 30.25" (W) X 17.5" (H)	2,500 LBS.	59.9" (L) X 30.25" (W) X 42.5" (H)	2,000 LBS.	59.9" (L) X 30.25" (W) X 12.5" (H)
<b>EXTRA-LARGE</b>	–	–	–	–	2,000 LBS.	70" (L) X 40" (W) X 21" OR 18.75" (H)	–	–	–	–
<b>WHEN TO USE</b>	IDEAL FOR SAFELY MOVING LARGE, BULKY SHEET AND PANEL GOODS		UNIQUE, CONVERTIBLE DESIGN IDEAL FOR SAFELY MOVING LARGE, BULKY SHEET AND PANEL GOODS AS WELL AS LONG ITEMS LIKE LUMBER AND PIPE		IDEAL FOR MOVING LARGE, HEAVY LOADS IN ALMOST ANY INDOOR AND OUTDOOR ENVIRONMENT		IDEAL FOR MOVING AND STORING LONG, BULKY ITEMS OF ROLL GOODS, PIPE, CARPET, LUMBER AND LINOLEUM		PERFECT FOR TEMPORARY MOVING AND STORING OF MATERIALS, PARTS, AND SUPPLIES	
<b>MATERIAL</b>	HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)		HIGH DENSITY POLYETHYLENE (HDPE)	
<b>CASTER &amp; SIZE OPTIONS</b>	POLYOLEFIN: 6" ON SMALL, 8" ON MEDIUM AND LARGE		POLYOLEFIN: 8"		TPR: 10" OR 12" PNEUMATIC: 10", 12" OR 16"		POLYOLEFIN: 6" OR 8"		TPR: 8"	
<b>COLOR</b>	BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED	
<b>POWDER-COATED METAL</b>	•		•		•		•		•	
<b>HANDLE RETAINER CLIPS</b>	•		•		•		•		•	
<b>TEXTURED DECK SURFACE</b>	•		•		•		•		•	
<b>MOLDED-IN TIE DOWN SLOTS (4)</b>	•		•		•		•		•	

# PLATFORM TRUCKS

## SELECTION GUIDE

To see our complete range of material handling solutions visit our online catalog at [rubbermaidcommercial.com](http://rubbermaidcommercial.com)

RCP-390  
#141734  
©2015 Rubbermaid Commercial Products LLC  
8900 Northpointe Executive Drive, Huntersville, NC 28078

