# The GuardDog SELF-CLOSING SAFETY GATE

# Description

The GuardDog Safety Gate is designed to match top and mid-rail heights of OSHA compliant guardrails, providing maximum opening coverage.

When the gate is installed with the top rail at OSHA's mandated guardrail height of 42" above the work surface, the bottom rail of the gate is at OSHA's nominal mid-rail height of 21".

The gates come in six sizes covering openings from 15" to

48". Each gate size can be laterally adjusted up to 6" (-3" to +3") to ensure proper fitting in the opening. Toe board adaptor kits are available for all sizes.



**Basic Use** 

The new Self Stopping GuardDog Safety Gate installs and adjusts easily without the need for a gate stop.

# standards.

- Features
- Tough, durable and easy to install

The GuardDog Safety Gate system provides maximum opening coverage for OSHA compliant guardrails.

**OSHA** Compliance

Fully compliant with all OSHA

- Universal Hinge Assembly fits various railing types up to 2" 0.D. or flat surface mounting. Adapter kits are available for larger or uniquely shaped railings
- Each gate is capable of swinging in either direction
- The self-closing feature employs two stainless steel torsion springs
- Five nominal sizes are available, and each is adjustable laterally up to 6"
- Available in three finishes: Powder Coat Safety Yellow, Hot-Dip Galvanized or 316 Stainless Steel. Special colors are available upon request
- The new Self Stopping GuardDog Safety Gate installs and adjusts easily without the need for a gate stop

Designed to match top and mid-rail heights of OSHA compliant guardrails, providing maximum opening coverage.

See reverse side for additional specifications and test results



4064 Peavey Road Chaska, MN 55318 866-933-2935 • 952-448-2935 Fax 952-448-3685 www.bluewater-mfg.com Email info@bluewater-mfg.com

# A COMPANY OF INNOVATION — **NOT** IMITATION



### Product Specifications



**Railings:** 14 GA tubing

Stainless Steel.

Hardware: U-Bolts and Universal Hinge Assembly: Fits railing types up to 2 inches

(51 mm) 0.D. or flat surface mounting, railing adaptor kit and self-closing springs

Finishes: Available in standard Powder Coat Yellow, Hot-Dip Galvanized and 316

Self-Closing Gate: Approved product: GuardDog Self-Closing Safety Gate: Provide maximum opening coverage when used with OSHA compliant guard rails.

**Approved product:** GuardDog Self-Closing Safety Gate: Provide maximum opening coverage when used with OSHA compliant guard rails.

**Standards:** System shall have top and mid rail in accordance with OSHA Standards – 29 CFR 1910.23 (a)(2)

Width: As indicated in Drawing

Height: Top Rail: 42 inches (1067 mm), minimum; Bottom Rail: 21 inches (533 mm)

#### New Self Stopping GuardDog Safety Gate

Our new Self Stopping GuardDog Safety Gate installs and adjusts easily without the need for a gate stop. This positive stopping mechanism is perfect for mezzanines and other areas which do not have adjoining structures.

> Self stopping action adjusts in seconds



| PROJECT:    |  |
|-------------|--|
| CONTRACTOR: |  |
| DATE:       |  |

