



The Mezzanine-Pivot Safety Gate

The MZ-Pivot Gate protects employees in elevated mezzanine loading areas. Its counterbalanced gates ensure that one gate is always between your employees and the edge of the platform.

The MZ-Pivot Gate is available in single or double pallet widths, breaks down for shipping efficiency and assembles easily with basic tools.

Easy to install

Available in carbon steel (galvanized or safety yellow powder coat)

Meets or exceeds OSHA, IBC and ANSI standards

Determining the proper gate size for your application only requires the measurement of the inside clear opening.

A36 Carbon Steel Galvanized

Model No.	Fits Clear Opening	Max Open Height	Est. Weight
MZ14-64	64”(w) x 42”(h)	81.65”	196 lbs
MZ14-113	113”(w) x 42”(h)	81.65”	244 lbs

A36 Carbon Steel with Safety Yellow Powder Coat

Model No.	Fits Clear Opening	Max Open Height	Est. Weight
MZ14-64PC	64”(w) x 42”(h)	81.65”	190 lbs
MZ14-113PC	113”(w) x 42”(h)	81.65”	244 lbs

Also available in Stainless Steel

The standard sizes listed above are stock items. FabEnCo also manufactures custom safety gates for wider openings or unusual handrail configurations. Please contact us with your special requirements.

The FabEnCo Pallet Gate is another fall protection option for mezzanine and platform material handling environments.

