



BESAM VERSAMAX FOLD
RH FOLD & SWING



NOTES:

THE STANDARD PACKAGE CONSISTS OF:
FRAME, NARROW STILE DOORS, PULL HANDLES AND BAR, GLASS STOPS
& BLOCKS FOR 1/4" TEMPERED GLASS, CONCEALED DOOR CLOSERS(S)
(NO 90 DEGREE HOLD OPEN), TOP AND BOTTOM PIVOTS, TOP ROLLER
TRACK AND VERTICAL WEATHERSTRIPPING.

DOUBLE PULL "C" HANDLES SUPPLIED FOR SWING DOOR
WHEN NO POSITIVE LATCH REQUIRED

MAX WEIGHT SWING DOOR 115 Lbs.
MAX WEIGHT FOLD DOOR 170 Lbs.

STANDARD FINISH:
CLEAR - AA-C23-A31
SPECIAL FINISHES ARE AVAILABLE


OPTIONS:

- ***** SMOKE SEALS
- CONCEALED SWEEPS
- POSITIVE LATCH
- FLUSH BOLT
- 1in. JAMBS
- ** 5/8" & 1" INSULATED GLASS


- *** - INSULATED GLASS NOT TO EXCEED 1/8in. PANES
- *** - TOP RAIL ALIGNMENT CAN VARY BY 5/16"
- *** - SMOKE SEAL PACKAGE INDEPENDENTLY TESTED TO UL1784.

(A)	1-3/4" JAMBS						
	DFW (A)	CDO (3) (B)	DOOR Fold (C)	DOOR Swing (D)	CDO (1) (E)	CDO (2) (F)	MASONRY OPENING
MIN. DFW	65-1/4"	51-7/8"	25-3/16"	36"	32-5/16"	19"	65-3/4" x 90"
MAX. DFW	120"	106-5/8"	67-15/16"	48"	44-5/16"	61-3/4"	120-1/2" x 90"
	KEY:	DFW-13 3/8"	DFW-D-4 1/16"		D- 3 11/16"	C- 6 3/16"	


(A)	1" JAMBS						
	DFW (A)	CDO (3) (B)	DOOR Fold (C)	DOOR Swing (D)	CDO (1) (E)	CDO (2) (F)	MASONRY OPENING
MIN. DFW	63-3/4"	51-7/8"	25-3/16"	36"	32-5/16"	19"	64-1/4" X 90"
MAX. DFW	118-1/2"	106-5/8"	67-15/16"	48"	44-5/16"	61-3/4"	119" X 90"
	KEY:1	DFW-11 7/8"	DFW-D-2 9/16"		D- 3 11/16"	C- 6 3/16"	



GLASS BLOCKING REQUIREMENTS



IN THE TOP
RAIL OF BOTH
FOLDING PANELS,
INCREASE HEIGHT
OF THE GLASS
BLOCKS TO
PROPERLY SUPPORT
DOORS



DWG NO.		US23-4900-01			
DRN BY	EMS	DATE	9/23/11	CHK BY	DATE
		REV.	D	DATE	5/29/11
Rev A- Updated Min Fold Door Size _____ _____ _____ _____ _____ _____					
ASSA ABLOY			_____ _____ _____		