



ASSA ABLOY



ASSA ABLOY Entrance Systems
1900 Airport Road
Monroe, NC 28110
Phone: 1-866-237-2687
specdeskna.besam@assaabloy.com

BESAM VERSAMAX ICU
TELESCOPIC BI-PART SLIDING DOOR SYSTEM
WITH SMOKE SEAL KIT


Patent Pending Design




TRACKLESS APPLICATION SHOWN. SURFACE AND RECESSED TRACKS ALSO AVAILABLE. FIXED SIDELITE ALSO AVAILABLE.



PLAN NOTE: DRAWING IS DIMENSIONED IN BOTH ENGLISH AND METRIC. REF. AS FOLLOWS: 1\"/>



NON REMOVABLE SECURITY TYPE GLAZING BEAD SYSTEM (TYP.) 1/4\"/>



* FACTORY APPLIED SEALS USED ON THIS SYSTEM TO SLOW OR RESTRICT PASSAGE OF SMOKE ARE CERTIFIED UNDER BHMA. SMOKE TESTED TO MEET REQUIREMENTS OF STANDARDS: UL1784, ANSI/NFPA105 2007, UBC7-2, PART 11 & B5476. PRESSURE/FIRE TESTED TO MEET REQUIREMENTS: UL10B, UL10C, UBC7-2 PART 1 & B5476

THE STANDARD PACKAGE CONSISTS OF: THE HEADER, FRAME, NARROW STILE DOOR(S) & SIDELITE(S), POSITIVE LATCH, GLASS STOPS & BLOCKS FOR 1/4\"/>

STANDARD FINISH: CLEAR - AA-M12C22A44, CLASS 1, .018 MM. SPECIAL FINISHES ARE AVAILABLE.

OPTIONS: SLOPED GLASS FOR CLEAN ROOM ENVIRONMENTS, MUNTINS, 1\"/>

DOOR PACKAGE WITH 1 3/4\"/>

MODEL NO.	CLEAR DOOR OPENING		OVERALL FRAME WIDTH		MASONRY OPENING WIDTH		ACTIVE & SIDELITE WIDTH	
	A	B	C	D	E	F	G	H
ICU-TE-6FBD-10	61 7/16\"/>							


CONSULT FACTORY FOR ALL CUSTOM CONFIGURATION SIZES OR SIZES OVER 14\"/>

DOOR PACKAGE WITH 1\"/>

MODEL NO.	CLEAR DOOR OPENING		OVERALL FRAME WIDTH		MASONRY OPENING WIDTH		ACTIVE & SIDELITE WIDTH	
	A	B	C	D	E	F	G	H
ICU-TE-6FBD-10	62 7/16\"/>							

CONSULT FACTORY FOR ALL CUSTOM CONFIGURATION SIZES OR SIZES OVER 14\"/>

SURFACE/RECESSED TRACK APPLICATIONS



VIEW FROM BREAK OUT SIDE
DOORS WILL BREAKOUT FROM ANY POSITION FOR SURFACE & RECESSED TRACK APPLICATIONS

TRACKLESS APPLICATIONS

DOORS WILL ONLY BREAK OUT WHEN IN THE FULLY OPEN POSITION FOR TRACKLESS APPLICATIONS

DWG NO.	US23-3400-33		
DRN BY	SS	DATE	3/29/10
CHK BY	DW	DATE	3/29/10
REV.	E	DATE	5/29/14

ASSA ABLOY