

Standard Packages

Unit Width	Slide Openings	Breakout Openings	Slide Panel Widths	Combined Sidelite Width	Rough Opening Width
14'-0" (4267)	3'-0" (914)	3'-3 1/2" (1003)	3'-6" (1067)	7'-1 1/2" (2172)	14'-0 1/2" (4280)
16'-0" (4877)	3'-6" (1067)	3'-9 1/2" (1156)	4'-0" (1219)	8'-1 1/2" (2451)	16'-0 1/2" (4877)

Unit Height: 7'-6" (2286)	Rough Opening Height: 7'-6 1/4" (2292)	Anodized Finish: Clear or Dark Bronze
Glazing: Standard unit prep'd for 1/4" (6) glass. Glass by others.		
Threshold: 1/2" (13) tall x 4" (102) wide (See page A5.3).		

Options

- Custom unit widths between 14'-0" & 16'-0".
 - Custom unit height to 8'-6".
 - Custom mid-rails, bottom rails and jambs.
 - Transom
 - Medium or wide stile construction (slide opening will be reduced).
 - Custom anodized or paint finish or stainless steel cladding
- See Architectural Specifications on p. A6.0 and Specification Details starting on p. A5.0.**

Installation and Operation

- Door perimeter mounted within rough opening with 1/4" minimum shim space at header & jambs. Finish floor not to exceed 1/4" out of level. (See page A.3)
- Electrical: Provide 120 VAC, 60 cycle, single phase, 15 amp service (in conduit) to each unit on dedicated 20 amp circuit breaker routed to header. Maximum current draw is 3.15 amps.
- Door actuated with header mounted motion sensors at interior and exterior (over each slide opening) for detection of traffic in each direction. Door closes after time delay expires. (See page A.4). Unit can also be set up for 1-way traffic thru each slide opening.
- Manual Locking: Exterior keylock and interior thumbturn provided at vertical strike rail. (Optional fail-safe or fail-secure autolock)

