


TECHNICAL DRAWING SPECIFICATION				UNLESS OTHERWISE SPECIFIED:			TITLE:				
				DIMENSIONS ARE IN MILIMETER [INCHES] Sanding Area : - - - - - Control Specs: Blue Wording			RES0106xx (DKG 5.5/1)				
										COMMENTS :Revise width from 140-141 to 139-141. (3.7.17)	
DRAWN BY		NAME		DATE		SIZE		DWG. NO.		REV	
WL LIM		WL LIM		1.6.13		A		PSS008		2	
APPROVED BY						SCALE: 1:1		MATERIAL : RESYSTA		SHEET 1 OF 1	
GM / CUSTOMER:											
Max. Area (Sanded)	Min Area (Sanded)	Max. Weight (Sanded)	Min. Weight (Sanded)								
1979 mm2	1838 mm2	3.07 kg/m	2.85 kg/m								