



TOP VIEW

FRONT VIEW

SIDE VIEW

9. INSTALLATION TEMPLATE MUST BE USED.
8. CBERGO-TRAY300 INCLUDES ABOVE ASSEMBLY, STORAGE MODULE #2336-2975, TILT TRAY #2336-3529-YE, MOUSE PAD #2307-2512, INSTALLATION TEMPLATE #3700-1073, AS WELL AS HARDWARE MOUNTING KIT #4180-0395 CONTAINING 8 EACH #8 x 5/8 SELF TAPPING SCREW.
7. PALM REST MAY BE REMOVED TO ACCOMODATE ALTERNATIVE KEYBOARDS.
6. REF P/N: CB319-500-L & CB319-500-R SLIDE ASSY.
5. HOLES OTHER THAN SHOWN AT ACCURIDE OPTION.
4. FINISH: ELECTRO-ZINC PLATED BLACK (SLIDE ASSY).
ELECTRO-POWDER COATED, BLACK (FORMED TRAY).
3. LUBRICANT: HIGH-LOW TEMPERATURE GREASE.
2. BALL BEARINGS: CARBURIZED STEEL.
1. MATERIAL: SLIDE MEMBERS AND COMPONENT PARTS:
WORK-HARDENED, COLD-ROLLED STEEL.

NOTES: UNLESS OTHERWISE SPECIFIED

ALL DIMENSIONAL TOLERANCES ARE ±.13"
[] DENOTES MM DIMENSIONS

SYM.	IS	DESCRIPTION	WAS	DATE	APPD.
REVISIONS					

THIS <i>Accuride</i> PRODUCT COVERED BY U.S. PATENTS #3205025, #3778120 AND OTHER U.S. PATENTS PENDING.					
CUSTOMER: ACCURIDE					
P/N:				REV.	
SCALE	DATE	CONTROLLING DOCUMENT			
N.T.S.		<input type="checkbox"/> ACCURIDE <input type="checkbox"/> CUSTOMER TOLERANCES NOT SHOWN			
DRAWN		in mm in mm .xxx ± .010 .25 Toler ± .13 3.3 .xx ± .030 .76 Holes ± .006 .15 Angular ± 1°			
APPROVED					
				<i>Accuride</i> DELUXE KEYBOARD PART NUMBER CBERGO-TRAY300	
				REV.	
THIS DOCUMENT IS FURNISHED FOR THE EXPRESS AND EXCLUSIVE PURPOSE OF CONVEYING INFORMATION TO CUSTOMERS AND SUPPLIERS OF ACCURIDE INTERNATIONAL INC. AND IS NOT TO BE DISCLOSED TO COMPETITIVE SOURCES.					