

MARS? STANDARD MODEL HEATER CHART

ELECTRIC HEATER DATA

MODEL	kW	208V 1Ø Amp (Ampacity)	240V 1Ø Amp (Ampacity)	208V 3Ø Amp (Ampacity)	240V 3Ø Amp (Ampacity)	460V 3Ø Amp (Ampacity)	575V 3Ø Amp (Ampacity)	TEMP RISE °F
E36	12	60.2 (75.3)	52.5 (65.6)	35.8 (44.8)	31.3 (39.1)	15.2 (19.1)	12.7 (15.9)	15
E38	12	60.2 (75.3)	52.5 (65.6)	35.8 (44.8)	31.3 (39.1)	15.2 (19.1)	12.7 (15.9)	15
E42	12	60.2 (75.3)	52.5 (65.6)	35.8 (44.8)	31.3 (39.1)	15.2 (19.1)	12.7 (15.9)	15
E48	12	60.2 (75.3)	52.5 (65.6)	35.8 (44.8)	31.3 (39.1)	15.2 (19.1)	12.7 (15.9)	15
E60	12	60.2 (75.3)	52.5 (65.6)	35.8 (44.8)	31.3 (39.1)	15.2 (19.1)	12.7 (15.9)	15
E64-2	24	CONTACT FACTORY	CONTACT FACTORY	71.7 (89.6)	62.6 (78.2)	30.5 (38.1)	25.4 (31.7)	15
E72-2	24	CONTACT FACTORY	CONTACT FACTORY	71.7 (89.6)	62.6 (78.2)	30.5 (38.1)	25.4 (31.7)	15
E78-2	24	CONTACT FACTORY	CONTACT FACTORY	71.7 (89.6)	62.6 (78.2)	30.5 (38.1)	25.4 (31.7)	15
E84-2	24	CONTACT FACTORY	CONTACT FACTORY	71.7 (89.6)	62.6 (78.2)	30.5 (38.1)	25.4 (31.7)	15
E96-2	24	CONTACT FACTORY	CONTACT FACTORY	71.7 (89.6)	62.6 (78.2)	30.5 (38.1)	25.4 (31.7)	15
E96-3	36	CONTACT FACTORY	CONTACT FACTORY	107.5 (134.4)	93.8 (117.3)	45.7 (57.2)	38.1 (47.6)	15
E108-3	36	CONTACT FACTORY	CONTACT FACTORY	107.5 (134.4)	93.8 (117.3)	45.7 (57.2)	38.1 (47.6)	15
E120-3	36	CONTACT FACTORY	CONTACT FACTORY	107.5 (134.4)	93.8 (117.3)	45.7 (57.2)	38.1 (47.6)	15
E144-3	36	CONTACT FACTORY	CONTACT FACTORY	107.5 (134.4)	93.8 (117.3)	45.7 (57.2)	38.1 (47.6)	15

For Other Wattages Available Consult Factory

1/2 HP STANDARD ELECTRIC HEATED MODELS