

SHALLOW EPS FORMS	EPS FORM	DEPTH MIN	DEPTH MAX	FLOW GPM
	10	8"	8 1/2"	606
	11	8 1/2"	9"	671
	12	9"	9 1/2"	736
	13	9 1/2"	10"	803
	14	10"	10 1/2"	869
	15	10 1/2"	11"	937
	16	11"	11 1/2"	1004
	17	11 1/2"	12"	1072
	18	12"	12 1/2"	1140
	19	12 1/2"	13"	1209
	20	13"	13 1/2"	1277
	21	13 1/2"	14"	1346
	22	14"	14 1/2"	1415
	23	14 1/2"	15"	1484
DEEP EPS FORMS	24	15"	15 1/2"	1554
	25	15 1/2"	16"	1623
	26	16"	16 1/2"	1693
	27	16 1/2"	17"	1762
	28	17"	17 1/2"	1832
	29	17 1/2"	18"	1902
	30	18"	18 1/2"	1972
	31	18 1/2"	19"	2042
	32	19"	19 1/2"	2113
	33	19 1/2"	20"	2183
	34	20"	20 1/2"	2253
	35	20 1/2"	21"	2324
	36	21"	21 1/2"	2394
	37	21 1/2"	22"	2465
	38	22"	22 1/2"	2535
	39	22 1/2"	23"	2606
	40	23"	23 1/2"	2676
	41	23 1/2"	24"	2747
	42	24"	24 1/2"	2818
	43	24 1/2"	25"	2889
	44	25"	25 1/2"	2959
	45	25 1/2"	26"	3030

(\* )CUSTOM SLOPES & DEPTHS AVAILABLE


# STEEL FRAMES & EPS FORMS ARE STANDARD 8'-0" LENGTHS

10	11	12	13	14	15	16	17	18	19	20	21	22	23
----	----	----	----	----	----	----	----	----	----	----	----	----	----

## SHALLOW EPS FORMS

24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45
----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----	----

## DEEP EPS FORMS



## NOTES:

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURER'S SPECIFICATIONS AND INSTALLATION INSTRUCTIONS.
2. A TRENCH SHALL BE EXCAVATED A MINIMUM OF 12" WIDER THAN THE OVERALL WIDTH OF THE STEEL FRAME (6" MINIMUM ON EACH SIDE)AND A MINIMUM OF 6 INCHES DEEPER THAN THE OVERALL DEPTH OF THE ECONODRAIN EPS FORM.
3. DO NOT SCALE DRAWINGS.

Copyright © 2014 MultiDrain Systems, Inc.

**MultiDrain**

1405 INDUSTRIAL DRIVE  
STATESVILLE, NC 28625  
(704) 508-1010  
1-800-433-1119  
www.multidrain.com

## EconoDrain® Series #10 Standard Rail & Bolt-In-Place Spacer Bar

FILE NUMBER:

CSI-ED-EPS-1096NR-14a

REV: 00

Proprietary rights of MultiDrain Systems, Inc. are included in the information disclosed herein. The recipient, by accepting this document, agrees that neither this document nor the information disclosed herein nor any part thereof shall be copied, reproduced or transferred for manufacturing or for any other purpose except as specifically authorized in writing by MULTIDRAIN.

**DISCLAIMER:** The customer and the customer's architects, engineers, consultants and other professionals are completely responsible for the selection, installation, and maintenance of any product purchased from MultiDrain, and EXCEPT AS EXPRESSLY PROVIDED IN MULTIDRAIN'S STANDARD WARRANTIES, MULTIDRAIN MAKES NO WARRANTY, EXPRESS OR IMPLIED, AS TO THE SUITABILITY, DESIGN, MERCHANTABILITY, OR FITNESS OF THE PRODUCT FOR CUSTOMER'S APPLICATION. Copies of MultiDrain's standard warranties are available upon request.