


Skylights conform to and exceed test requirements of CAN/CGSB-63.14M89, "Plastic Skylights", Class D, Type 2 or Type 3.

Skylights designed to be installed on flat roofs, and are similar to model CL, including insulated curb. Pyramid glazing is added for enhanced visual effect.

Custom sizes are available upon request



Model P-CL Available Sizes			
Model #	B x B Dimensions	Pyramid Color	QTY
P-CL 2852	22¼" x 46¼" (565mm x 1175mm)		
P-CL 3636	30¼" x 30¼" (768mm x 768mm)		
P-CL 3652	30¼" x 46¼" (768mm x 1175mm)		
P-CL 3676	30¼" x 69½" (768mm x 1765mm)		
P-CL 4242	37" x 37" (940mm x 940mm)		
P-CL 4280	37" x 75" (940mm x 1905mm)		
P-CL 5252	46¼" x 46¼" (1175mm x 1175mm)		
P-CL 5260	46¼" x 55" (1175mm x 1397mm)		
P-CL 5276	46¼" x 69½" (1175mm x 1765mm)		
P-CL 5296	46¼" x 89½" (1175mm x 2273mm)		
P-CL 6060	55" x 55" (1397mm x 1397mm)		
P-CL 6076	55" x 69½" (1397mm x 1765mm)		
P-CL 7272	67" x 67" (1702mm x 1702mm)		
P-CL 8080	75" x 75" (1905mm x 1905mm)		
P-CL 9696	89½" x 89½" (2273mm x 2273mm)		
P-CL CUST.			
P-CL CUST.			

Specifications:

Skylight shall be factory assembled Model No. _____ P-CL as manufactured by Artistic Skylight Domes Ltd. Vaughan, Ontario. Glazing shall consist of, sealed double acrylic pyramids (or sealed triple pyramids) of clear, white, bronze, or grey. The skylight shall consist of rigid high-impact extruded vinyl curb frame (superior in thermal conductivity to aluminum) which incorporates a high capacity, 10 degree sloped condensation gutter with drainage to exterior, co-extruded rubber draft seal. The retaining cap frame shall be extruded, mill finish (optional baked enamel), 6063-T5 aluminum alloy with heliarc welded corners. Curb shall be, 9" high (optional 12") mill finish aluminum, 2 piece construction of .050 outer wall and .050 inner wall, with 2" thick insulation and 3" aluminum mounting flange.

Pyramid Colors Available

Pyramid Color	Colour Code	Pyramid Color	Colour Code
Clear	- C	White	- W
Bronze	- B	Grey	- G

Project:	Architect:
Contractor:	Approved By:
	Date:

