




Innovative Products

2395 West 4th Avenue Denver, CO 80223 USA  
 Phone 303.892.0400 Toll Free 800.333.4234 Fax 303.825.5988  
 EMail info@BisonIP.com Web www.BisonIP.com


Get CEU Credits, Details & Specifications online at BisonIP.com

**SCREWJACK**  
 Adjustable Deck Supports



12" O.C. JOIST SPACING (DECKING SPAN)			
JOIST SIZE	JOIST SPAN	BEAM SIZE	PEDESTAL SPACING
2x6	10' - 0"	4x6 OR (2) 2x6	24" O.C.
2x8	13' - 2"	4x8 OR (2) 2x8	24" O.C.
2x10	16' - 10"	4X10 OR (2) 2x10	24" O.C.
16" O.C. JOIST SPACING (DECKING SPAN)			
JOIST SIZE	JOIST SPAN	BEAM SIZE	PEDESTAL SPACING
2x6	9' - 1"	4x6 OR (2) 2x6	24" O.C.
2x8	12' - 0"	4x8 OR (2) 2x8	24" O.C.
2x10	15' - 2"	4X10 OR (2) 2x10	24" O.C.
24" O.C. JOIST SPACING (DECKING SPAN)			
JOIST SIZE	JOIST SPAN	BEAM SIZE	PEDESTAL SPACING
2x6	7' - 11"	4x6 OR (2) 2x6	24" O.C.
2x8	10' - 2"	4x8 OR (2) 2x8	24" O.C.
2x10	12' - 5"	4X10 OR (2) 2x10	24" O.C.

\*\*\* CHARTS ARE SHOWN USING HEM-FIR #2 LUMBER OR BETTER.



**NOTE:**  
 DECKING AND JOIST SPANNING CAPABILITIES VARY DEPENDING ON THE TYPE OF WOOD OR COMPOSITE MATERIALS BEING USED. CODE REQUIREMENTS ALSO VARY PER LOCATION. FOR THESE REASONS, THIS DIAGRAM AND CHART ARE FOR CONVENIENCE ONLY, AND IT IS THE INSTALLERS RESPONSIBILITY TO ENSURE THE DECK MEETS CODE REQUIREMENTS.

- GENERAL NOTES:** APPLY TO ALL OF THE ABOVE PRODUCTS
1. INSTALLATION MUST BE COMPLETED IN ACCORDANCE WITH BISON INNOVATIVE PRODUCTS SPECIFICATIONS.
  2. DRAWINGS NOT TO SCALE.
  3. CONTRACTOR'S NOTE: FOR PRODUCT AND COMPANY INFORMATION VISIT [www.BisonIP.com](http://www.BisonIP.com) REFERENCE B-061.

**JOIST AND PLANK DECK**  
 JOIST AND PLANK DECK AND SPANNING CHART