



## MODEL # 3300

**TABLE #1  
SECTION CHART**

DOOR HEIGHT	NUMBER OF SECTIONS
8'0"	3
8'2" - 8'0"	4
8'2" - 10'0"	5
10'2" - 12'0"	6
12'2" - 14'0"	7
14'2" - 16'0"	8
16'2" - 18'0"	9

NOTE: DOOR HEIGHT IS AVAILABLE IN 3" INCREMENTS

**TABLE #2  
PANEL CHART**

DOOR WIDTH	NUMBER OF PANELS
7'0" - 9'2"	2
9'4" - 13'2"	3
13'4" - 16'2"	4
16'4" - 20'2"	5
20'4" - 24'2"	6

NOTE: DOOR WIDTH IS AVAILABLE IN 2" INCREMENTS

**TABLE #3  
LITE AVAILABILITY CHART**

WINDOW SIZE	DOOR WIDTH	LITES PER SECTION
8" x 24"	7'0" - 9'2"	2
	9'4" - 13'2"	3
	13'4" - 16'2"	4
	16'4" - 20'2"	5
	20'4" - 24'2"	6
14" x 28"	8'0" - 9'2"	2
	9'4" - 11'0"	3
	11'2" - 13'2"	3
	13'4" - 15'2"	4
14" x 40"	15'4" - 16'2"	4
	8'0" - 9'2"	2
	9'4" - 11'0"	1 (CENTER PANEL)
	11'2" - 13'2"	3
14" x 40"	13'4" - 15'2"	2 (CENTER PANELS)
	15'4" - 16'2"	4

**TABLE #4  
REINFORCEMENT CHART**

DOOR HEIGHT	DOOR WIDTH				
	UP TO 15'2"	15'4"- 17'2"	17'4"- 18'2"	18'4"- 23'2"	23'4"- 24'2"
UP TO 8'1"	NONE	3 ea. 2-1/4"	3 ea. 2-1/4"	4 ea. 3"	4 ea. 4" C-CHANNEL
8'3" TO 10'1"	NONE	3 ea. 2-1/4"	5 ea. 2-1/4"	5 ea. 3"	5 ea. 4" C-CHANNEL
10'3" TO 12'1"	NONE	4 ea. 2-1/4"	6 ea. 2-1/4"	6 ea. 3"	6 ea. 4" C-CHANNEL
12'3" TO 14'1"	NONE	4 ea. 2-1/4"	7 ea. 2-1/4"	7 ea. 3"	7 ea. 4" C-CHANNEL
14'3" TO 16'1"	NONE	5 ea. 2-1/4"	8 ea. 2-1/4"	8 ea. 3"	8 ea. 4" C-CHANNEL
16'3" TO 18'1"	NONE	5 ea. 2-1/4"	9 ea. 2-1/4"	9 ea. 3"	9 ea. 4" C-CHANNEL