





2.67" x 1/2" CORR. STANDARD TRIM SKETCHES

<div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> GA. # _____ COLOR _____ </div> <div style="border: 1px solid black; width: 50px; height: 30px; margin-bottom: 10px;"></div>  <p style="text-align: center;">REQ'D: _____ PCS. @ 10'-0" LG.</p>	<div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> GA. # _____ COLOR _____ </div> <div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> 5 1/2" </div>  <p style="text-align: center;">REQ'D: _____ PCS. @ 10'-0" LG.</p>
"SR1" BASE ROOF	"BD1" BASE TRIM
<div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> GA. # _____ COLOR _____ </div> <div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> 7 3/4" </div>  <p style="text-align: center;">REQ'D: _____ PCS. @ 10'-0" LG.</p>	<div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> GA. # _____ COLOR _____ </div> <div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> 4 3/8" </div>  <p style="text-align: center;">REQ'D: _____ PCS. @ 10'-0" LG.</p>
"ST1" SILL TRIM	"EJ1" EDGING TRIM

NOTES:

1. ALL TRIM IS MANUFACTURED IN 10'-0" LENGTHS UNLESS SPECIFIED OTHERWISE.
2. MAXIMUM LENGTH OF TRIM IS 10'-0".
3. PLEASE INSERT GAUGE OF MATERIAL IN SPACES PROVIDED.
4. PLEASE INSERT COLOR OF MATERIAL IN SPACES PROVIDED.
5. PLEASE INSERT QUANTITY DESIRED WHERE SHOWN.
6. PLEASE INSERT REQ'D DIMENSIONS.



BOX 515 RAILROAD STREET
 SANDY LAKE, PENNSYLVANIA 16145-0515
 PHONE: 800-245-0396 ° FAX: 724-376-3864

2.67" x 1/2" Corrugated
 Standard Details

DRAWN BY: RW

DATE: 2/17/00

DRAWING NO.

REVISED BY: CANON
 K. Kemmer

DATE: 5-30-20

2.67" x 1/2" - 15