


Solid Phenolic Core Series 30 - Floor Mounted



Scope - Solid Phenolic Core toilet, shower and dressing compartments are fabricated of SPC with matte finish high pressure melamine fusion welded to surface to form one piece unit which will not delaminate, edges are black solid phenolic resin, Completely water resistant, impervious to steam, soap, and detergents. Will not mildew.

Panels - Will be 1/2" thick

Doors - Will be 3/4" thick

30 Series Pilasters - Will be 3/4" thick. Pilasters are to be anchored to the floor with standard 3/8" threaded rod, hex nut, and washer to provide vertical adjustment and necessary strength.

Hardware - To be heavy casting non-ferrous alloy, chrome-plated and aluminum. Toilet compartment will be provided with all hardware and fasteners for a complete installation for a standard installation with masonry block walls and concrete floors.

Brackets - Chrome plated stirrup brackets. Single ear will be used at pilaster to wall and end panel to walls. Double ear brackets will be used at intermediate panel to walls. U brackets will be use for panels to back of pilasters.

Door Hardware - Aluminum wrap around hinges. To be secured to pilaster and doors with thru-bolts. ADA doors will be provided with ADA coat hook, double sided door pull, and door bumper. Standard doors will be provided with combination coat hook / bumper.

Shoes - To be 5" high, .031 stainless steel.

Natural Almond D30-60	Fashion Grey D381-60	Frosty White 1573-60
Grey Glace 4142-60	Graphite Nebula 4623-60	Haze D97-60
Midway 4936-60	Arcade 4938-60	Natural Tigris 4669-60
Green Tigris 4667-60	Brittany Blue D321-60	Aqua Fizz 4934-60
Windswept 4793-60	Pewter Mesh 4878-60	Steel Mesh 4879-60
Pomegranate 4914-60	Navy Legacy 4651-60	Windswept Bronze 4794-60
Carbon EV 4820-60	Black 1595-60	Cream Fizz 4933-60
Pewter Brush 4779-60	Oiled Soapstone 4882-60	Antique Brush 4823-60
Satin Stainless 4830-60	Evening Tigris 4674-60	Almond Leather 2932-60

Hinge Options

- Aluminum Wrap Around Hinge (Standard)
- Stainless Steel Vault Hinge
- Stainless Steel Surface Mounted (1500GS)
- Continuous Aluminum Spring Hinge (GXA2000)
- Continuous Stainless Steel Spring Hinge (JN2000)
- Continuous Stainless Steel Gravity Hinge (JN7789)

Door Hardware Options

- Aluminum Surface Mounted Latch & Keeper
- Chrome Plated Surface Mounted Latch & Keeper
- Stainless Steel Surface Mounted Latch & Keeper

Classification

- Class "B" Fire Rated (Standard)
- Class "A" Fire Rated

Bracket Options

- Chrome Plated Stirrup Brackets (Standard)
- Stainless Steel Stirrup Brackets
- Continuous Aluminum Brackets
- Continuous Stainless Steel Brackets

Other Options

- Cutouts
- Aluminum Privacy Strips
- No Sight Strike