



**NOTES:**

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
2. ENTRY BARRIER SHOWN (GATE ARM ON ATTACK SIDE)
3. CRASH RATING: 15000LB (6800KG) @ 30MPH (50KPH) M30 (K4)
4. REBAR REQUIRED: 267LB #5

**PROPRIETARY AND CONFIDENTIAL**  
 THIS DRAWING, UNLESS OTHERWISE NOTED, REMAINS CONFIDENTIAL PROPERTY AND IS DESCRIBED AS TRADE SECRET. IT SHALL NOT BE DISCLOSED, REPRODUCED OR USED FOR MANUFACTURE, DESIGN OR CONSTRUCTION WITHOUT THE EXPRESS AUTHORIZATION OF SECUREUSA, INC. THE RECIPIENT BY ACCEPTING THIS DRAWING, ASSUMES CUSTODY THEREOF AND UNDER THE ABOVE TERMS AGREES NOT TO ALLOW USE BY UNAUTHORIZED PERSONS.  
 ©2006 SECUREUSA INC. (ALL RIGHTS RESERVED)

PATH: Z:\Product Drawing Files\Surface Mount Barrier\31XX\GENERAL ARRANGEMENTS\M30\

CAD GENERATED DRAWING NO MANUAL REVISIONS ALLOWED	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
DIMENSIONS ARE: INCHES	
X/X	±1/16
X	±0.05
XX	±0.02
XXX	±0.01
XXXX	±0.001
ANGLE ±30MIN	
BREAK ALL SHARP EDGES	
DO NOT SCALE DRAWING	
THIRD ANGLE PROJECTION	

 <b>SecureUSA</b> Inc.® Perimeter Defense Solutions		<b>SecureUSA, Inc.</b> 4250 Keith Bridge Road Cumming, GA 30041 Toll Free: 888.222.4559/Facsimile: 770.889.7939 <a href="http://www.SecureUSA.net">www.SecureUSA.net</a>	
		DRAWN BY: M.S CHECKED: R.S APVD:	DESCRIPTION: 31 IN 10 FT M30 SHALLOW MOUNTED FUTUREWEDGE BARRIER
MATERIAL: FINISH: DATE: 7/15/2011	SIZE: B DWG NO: SHS31 10-4 LH ENTRY	REV:	SCALE: 1:32 WEIGHT: 3964.40
		SHEET 1 OF 1	