



1. APPLY GE ELEMEX 5000 LIQUID FLASHING TO THE ROUGH OPENING AT A NOMINAL 20-40 MILS (508-1016  $\mu$ ) THICKNESS. SPREAD/TROWEL THE GE ELEMEX 5000 LIQUID FLASHING TO A MINIMUM OF 3" (75 MM) ONTO WALL AND 3" (75 MM) INTO ROUGH OPENING. LIQUID FLASHING SHOULD BE CONTINUOUS AND SMOOTH WHILE FREE OF POCKETS, VOIDS AND/OR PINHOLES.
2. APPLY/TOOL GE LIQUID FLASHING TO INSIDE CORNERS OF ROUGH OPENING TO ENSURE SEAMLESS COVERAGE.

**NOTES:**

- ENSURE ROUGH OPENINGS ARE DRY, CLEAN AND FREE OF DIRT, DEBRIS AND CONTAMINANTS.
- GE ELEMEX 5000 LIQUID FLASHING MAY BE INSTALLED BEFORE OR AFTER THE APPLICATION OF GE ELEMEX 2600 AWB. WHEN INSTALLING BEFORE, THE CUT EDGES OF GYPSUM SHEATHING MAY NEED TO BE COATED WITH GE ELEMEX 2600 AWB.
- ENSURE GE ELEMEX 2600 AWB IS DRY TO THE TOUCH PRIOR TO THE APPLICATION OF GE ELEMEX 5000 LIQUID FLASHING.
- IT IS RECOMMENDED TO CHECK ADHESION OF GE PRODUCTS TO STEEL STUDS PRIOR TO USE. GE SS80 PRIMER CAN BE USED IF NEEDED.
- THE USE OF USM ULTRASpan\* PRE-CURED SILICONE MOLDED CORNERS MAY ALSO BE UTILIZED. ENSURE GE ELEMEX 5000 LIQUID FLASHING EXTENDS A MIN. 2" (50 MM) OVER USM ULTRASpan CORNERS PROPERLY EMBEDDED IN GE ELEMEX 5000 LIQUID FLASHING.
- SEE GE ELEMEX 2600 AWB DATA SHEET FOR LIST OF ADDITIONAL ACCEPTABLE GE SEALANTS/LIQUID FLASHING.

**ROUGH OPENING - METHOD A: ELEMEX 5000 LIQUID FLASHING  
GE ELEMEX\* 2600 AIR AND WATER-RESISTIVE BARRIER SYSTEM**

**DETAIL #:** AWB-05

**SCALE:** N.T.S.

**DATE:** 2017-03-27

THE ABOVE DETAIL IS FOR ILLUSTRATION PURPOSES ONLY. IT IS INTENDED AS A GUIDELINE TO ASSIST MOMENTIVE PRODUCT USERS IN DEVELOPING PROJECT SPECIFIC DETAILS. CONSULT APPROPRIATE SPECIFICATION DOCUMENTS, DATA SHEETS, BUILDING CODES AND ANY OTHER INFORMATION DEEMED NECESSARY FOR SPECIFIC REQUIREMENTS. MOMENTIVE PRODUCT USERS ARE RESPONSIBLE FOR DETERMINING THE SUITABILITY OF MOMENTIVE PRODUCTS FOR THE PARTICULAR APPLICATION AND ALL RELATED PROJECT DETAILS. MOMENTIVE MAKES NO WARRANTY, EXPRESS OR IMPLIED, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OF ITS PRODUCTS IN ANY USER'S APPLICATION. ANY SALE OF PRODUCTS OR DELIVERY OF CUSTOMER SUPPORT AND ADVICE BY MOMENTIVE PERFORMANCE MATERIALS INC. AND/OR ANY OF ITS AFFILIATES ("MOMENTIVE") IS MADE EXCLUSIVELY UNDER MOMENTIVE'S STANDARD CONDITIONS OF SALE, WHICH ARE AVAILABLE AT [WWW.GE.COM/SILICONES](http://WWW.GE.COM/SILICONES).