



**NOTES:**

- ROUGH OPENING MUST PROPERLY TREATED PRIOR TO WINDOW INSTALLATION. SEE DETAIL AWB-05, AWB-06 OR AWB-07.
- ENSURE GE ELEMEX 5000 LIQUID FLASHING IS INSTALLED A MINIMUM 2" (50 MM) ONTO SHEATHING AND TOOLED SMOOTH AT PROPER THICKNESS.
- IT IS RECOMMENDED TO CHECK ADHESION OF GE PRODUCTS TO FLANGE PRIOR TO USE. GE SS80 PRIMER CAN BE USED IF NEEDED.
- GE RF100 REINFORCING FABRIC EMBEDDED IN GE ELEMEX 2600 AWB OR GE ULTRASPAN\* UST2200 SILICONE TRANSITION SHEET EMBEDDED IN GE ELEMEX 5000 LIQUID FLASHING MAY ALSO BE UTILIZED TO TREAT WINDOW FLANGE.
- DO NOT BLOCK DRAINAGE AT WINDOW SILL.
- SEE GE ELEMEX 2600 AWB DATA SHEET FOR LIST OF ADDITIONAL ACCEPTABLE GE SEALANTS/LIQUID FLASHING.

**WINDOW FLANGE TREATMENT  
GE ELEMEX® 2600 AIR AND WATER-RESISTIVE BARRIER SYSTEM**

**DETAIL #:**            **AWB-08**

THE ABOVE DETAIL IS FOR ILLUSTRATION PURPOSES ONLY. IT IS INTENDED AS A GUIDELINE TO ASSIST MOMENTIVE PRODUCT USERS IN DEVELOPING PROJECT SPECIFIC DETAILS. CONSULT APPROPRIATE SPECIFICATION DOCUMENTS, DATA SHEETS, BUILDING CODES AND ANY OTHER INFORMATION DEEMED NECESSARY FOR SPECIFIC REQUIREMENTS. MOMENTIVE PRODUCT USERS ARE RESPONSIBLE FOR DETERMINING THE SUITABILITY OF MOMENTIVE PRODUCTS FOR THE PARTICULAR APPLICATION AND ALL RELATED PROJECT DETAILS. MOMENTIVE MAKES NO WARRANTY, EXPRESS OR IMPLIED, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OF ITS PRODUCTS IN ANY USER'S APPLICATION. ANY SALE OF PRODUCTS OR DELIVERY OF CUSTOMER SUPPORT AND ADVICE BY MOMENTIVE PERFORMANCE MATERIALS INC. AND/OR ANY OF ITS AFFILIATES ("MOMENTIVE") IS MADE EXCLUSIVELY UNDER MOMENTIVE'S STANDARD CONDITIONS OF SALE, WHICH ARE AVAILABLE AT [WWW.GE.COM/SILICONES](http://WWW.GE.COM/SILICONES).

**SCALE:**                    **N.T.S.**

**DATE:**                    **2017-03-27**