



NOTES:

- ENSURE SURFACE IS DRY, CLEAN AND FREE OF DIRT, DEBRIS AND CONTAMINANTS.
- CLEAN LOOSE MORTAR AND OTHER CONTAMINATIONS WHERE NECESSARY BY WIRE BRUSH OR SIMILAR ABRASION TO PROVIDE A STABLE CLEAN SURFACE FOR APPLICATION.
- MASONRY JOINTS SHALL BE STRUCK FLUSH.
- CRACKS OR VOIDS AT JOINTS GREATER THAN 1/16" (2 MM) AND UP TO 1/2" (13 MM) SHALL BE FILLED (ROUTED AND FILLED WHERE NECESSARY) WITH A TROWEL APPLICATION OF GE ELEMEX 5000 LIQUID FLASHING PRIOR TO APPLICATION OF GE ELEMEX 2600 AWB. REPAIR LARGER CRACKS OR VOIDS WITH NON-SHRINKING GROUT OR OTHER APPROPRIATE PATCHING MATERIAL.
- WHEN SPRAY APPLYING OVER CMU, BACK ROLLING WILL BE REQUIRED TO ENSURE A PIN HOLE FREE APPLICATION.
- SEE GE ELEMEX 2600 AWB DATA SHEET FOR LIST OF ADDITIONAL ACCEPTABLE GE SEALANTS/LIQUID FLASHING.

CMU APPLICATION DETAIL
GE ELEMEX 2600* AIR AND WATER-RESISTIVE BARRIER SYSTEM

DETAIL #: AWB-24

SCALE: N.T.S.

DATE: 2017-03-27

THE ABOVE DETAIL IS FOR ILLUSTRATION PURPOSES ONLY. IT IS INTENDED AS A GUIDELINE TO ASSIST MOMENTIVE PRODUCT USERS IN DEVELOPING PROJECT SPECIFIC DETAILS. CONSULT APPROPRIATE SPECIFICATION DOCUMENTS, DATA SHEETS, BUILDING CODES AND ANY OTHER INFORMATION DEEMED NECESSARY FOR SPECIFIC REQUIREMENTS. MOMENTIVE PRODUCT USERS ARE RESPONSIBLE FOR DETERMINING THE SUITABILITY OF MOMENTIVE PRODUCTS FOR THE PARTICULAR APPLICATION AND ALL RELATED PROJECT DETAILS. MOMENTIVE MAKES NO WARRANTY, EXPRESS OR IMPLIED, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OF ITS PRODUCTS IN ANY USER'S APPLICATION. ANY SALE OF PRODUCTS OR DELIVERY OF CUSTOMER SUPPORT AND ADVICE BY MOMENTIVE PERFORMANCE MATERIALS INC. AND/OR ANY OF ITS AFFILIATES ("MOMENTIVE") IS MADE EXCLUSIVELY UNDER MOMENTIVE'S STANDARD CONDITIONS OF SALE, WHICH ARE AVAILABLE AT WWW.GE.COM/SILICONES.