



**METHOD A**

**A1:** APPLY GE ELEMEX 5000 LIQUID FLASHING AND TROWEL OVER THE JOINT SEAM TO A NOMINAL 1-1/2" (38 MM) WIDTH CENTERED ON THE JOINT AT A MINIMUM THICKNESS OF 20-40 MILS (508-1016 μ).

**METHOD B**

**B1:** APPLY A LIBERAL COAT (MIN. 10 MILS [254 μ]) OF GE ELEMEX 2600 AWB IN SUFFICIENT WIDTH TO ACCOMMODATE GE RF100 REINFORCING FABRIC.

**B2:** WHILE STILL WET, SET GE RF100 REINFORCING FABRIC INTO THE GE ELEMEX 2600 AWB AND CENTER ON JOINT.

**B3:** APPLY A SECOND COAT (MIN. 10 MILS [254 μ]) OF GE ELEMEX 2600 AWB IMMEDIATELY OVER THE GE RF100 REINFORCING FABRIC ENSURING A PIN HOLE FREE APPLICATION IS ACHIEVED.

**NOTES:**

- SHEATHING JOINTS MAY BE TREATED BEFORE OR AFTER THE APPLICATION OF GE ELEMEX 2600 AWB.
- ENSURE GE ELEMEX 2600 AWB IS DRY TO THE TOUCH PRIOR TO THE APPLICATION OF GE ELEMEX 5000 LIQUID FLASHING.
- METHOD A CAN BE USED UP TO 1/4" (6 MM) WITHOUT STUD BACKING AND UP TO 1/2" (13 MM) WITH STUD BACKING.
- THE USE OF A NOTCHED TROWEL MAY BE UTILIZED TO SIMPLIFY THE APPLICATION OF GE ELEMEX 5000 LIQUID FLASHING.
- FOR GAPS > 1/2" (13 MM) SEE DETAIL A102.
- SEE GE ELEMEX 2600 AWB DATA SHEET FOR LIST OF ADDITIONAL ACCEPTABLE GE SEALANTS/LIQUID FLASHING.

**SHEATHING JOINT & FASTENER TREATMENT**  
**GE ELEMEX® 2600 AIR AND WATER-RESISTIVE BARRIER SYSTEM**

**DETAIL #:** AWB-01

THE ABOVE DETAIL IS FOR ILLUSTRATION PURPOSES ONLY. IT IS INTENDED AS A GUIDELINE TO ASSIST MOMENTIVE PRODUCT USERS IN DEVELOPING PROJECT SPECIFIC DETAILS. CONSULT APPROPRIATE SPECIFICATION DOCUMENTS, DATA SHEETS, BUILDING CODES AND ANY OTHER INFORMATION DEEMED NECESSARY FOR SPECIFIC REQUIREMENTS. MOMENTIVE PRODUCT USERS ARE RESPONSIBLE FOR DETERMINING THE SUITABILITY OF MOMENTIVE PRODUCTS FOR THE PARTICULAR APPLICATION AND ALL RELATED PROJECT DETAILS. MOMENTIVE MAKES NO WARRANTY, EXPRESS OR IMPLIED, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OF ITS PRODUCTS IN ANY USER'S APPLICATION. ANY SALE OF PRODUCTS OR DELIVERY OF CUSTOMER SUPPORT AND ADVICE BY MOMENTIVE PERFORMANCE MATERIALS INC. AND/OR ANY OF ITS AFFILIATES ("MOMENTIVE") IS MADE EXCLUSIVELY UNDER MOMENTIVE'S STANDARD CONDITIONS OF SALE, WHICH ARE AVAILABLE AT [WWW.GE.COM/SILICONES](http://WWW.GE.COM/SILICONES).

**SCALE:** N.T.S.

**DATE:** 2017-03-27