


# KEY TO PRECISION AUTOMATIC ELECTRIC DISAPPEARING STAIRWAY



## MEASUREMENTS

A 38°  
 B -  
 \*C -  
 D -  
 E -  
 F -  
 X -

## ALUMINUM CONSTRUCTION

### STANDARD:

ROUGH OPENING IN CEILING 30" X 72"

- ① FRAME 1/8" STEEL X 28-1/2" X 71" X -  
 (USE 52" ANGLE FRAME IF DROPPED CEILING  
 IS 13" OR MORE FOR HEAD CLEARANCE)

EXACT FINISHED CEILING HEIGHT  $\pm 1/2"$ : -

EXACT FLOOR TO FLOOR DIMENSION  $\pm 1/2"$ : -

- ② HAND-GUIDE RAILS 1-1/16"OD GALVANIZED  
 ③ SEALED BALL BEARINGS  
 ④ 1/3 HP 115-VOLT INSTANTLY REVERSIBLE MOTOR DIRECT-CONNECTED  
 TO A REDUCTION GEAR DRIVE, COMPLETE WITH CONTACTORS &  
 PREWIRED TO CONTROL SWITCHES.  
 ⑤ STRINGERS 7" X .230" CHANNEL  
 ⑥ TREADS 6" X 20-3/16" X .225" CHANNEL COVERED WITH NON-SKID  
 SAFETY TREAD  
 ⑦ DOOR PANEL 1/8" SHEET ALUMINUM  
 ⑧ BATTERY BACK-UP (NOT SHOWN)  
 (USED IN CASE OF POWER FAILURE TO LOWER ONLY)

EACH STAIRWAY IS FACTORY TESTED BEFORE SHIPMENT  
 & IS SHIPPED IN A HEAVY PROTECTIVE CRATE.

## OPTIONS-(Check if Required)


KEY SWITCH AT LOWER LEVEL ----- ☐

WARNING BUZZER, WHEN STAIR IS IN USE ----- ☐

\* MEASURED FROM FLOOR TO FLOOR

NOT TO SCALE

AEKEY

 <b>Precision Ladders, LLC</b> P.O. Box 2279 Morristown, TN 37816-2279 Ph: (423) 586-2265 Fax: (423) 586-2091 www.PrecisionLadders.com	DWG. CHECK	ARCH'T OR ENG'R.	PROJECT		PRECISION REP	
	BUILT BY:	PURCHASE ORDER	WORK ORDER	PURCHASER		SERIAL#
	CHECKED BY:	DRAWN BY: JBR	DATE 12/23/09	MODEL# AE-	QTY. 1	