

Harlequin's 'latch and lock' system




Diagram of 'brickwork fashion'

American Harlequin Corporation
1531 Glen Avenue
Moorestown, NJ 08057

(800) 642 6440
contact@harlequinfloors.com
harlequinfloors.com

PHILADELPHIA
FORT WORTH
LOS ANGELES
LAS VEGAS
LONDON
PARIS
BERLIN
LUXEMBOURG
MADRID
SYDNEY
HONG KONG
TOKYO

The Company reserves the right to make any variation in design or construction of the material described.
© Harlequin Floors 02/2021.

Harlequin Liberty HD™ is a further development of our renowned Liberty panel system, designed with enhanced durability in mind, for more challenging environments. Installed permanently or as a portable floor, panels are laid in a brickwork fashion onto the sub-floor so that cross joins do not coincide. The panels join together by a rounded tongue and groove and are secured using our 'one turn of the key' latch and lock mechanism.

Harlequin Liberty HD panels are overlaid with a black polymer resin on both sides and have a textured, high grip pattern on the top surface, which is high water-resistant, anti-slip and weatherproof.

Harlequin Liberty HD panels can be finished by choosing an appropriate Harlequin vinyl performance floor from our range. For permanent and semi-permanent use, installation can be carried out either by the customer themselves or by our highly-skilled technical team.

Harlequin sprung floor panels and the accompanying portable Harlequin vinyl performance floor can also be stored in carts, providing an easy and safe way for stage crew to move them on tour or around a venue.

**Harlequin Liberty HD available by special order only.*

Specification Guide

Permanent or Portable	Both
Full Size Panel	96" x 48"
Half Size Panel	48" x 48"
Weight	86 lbs (Full Size) 43 lbs (Half Size)
Thickness	1 1/2"
Testing Standards	DIN 18032-2
Average Shock Absorption	67%
Vertical Deformation	4.1mm
Area Deflection	12.8%
Rolling Load	>1500 N
Maximum Point Load	2482 lbs

Harlequin Sprung Floor Application Guide

Along with Harlequin Liberty HD, we offer additional sprung flooring options, which are listed below along with the recommended surface. These recommendations are based on experience and customer preference only. Please contact a Flooring Specialist to determine which option best suits your requirements.

✓ = We recommend.

	Allegro	Cascade	Fiesta	FreeStyle	Hardwood	Hi-Shine	Marine	Reversible	Reversible Pro	Standfast	Studio	Studio B
Activity		✓	✓	✓	✓		✓			✓	✓	✓
AeroDeck		✓	✓	✓		✓	✓	✓	✓	✓	✓	✓
Flexity		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Liberty HD		✓		✓		✓		✓	✓	✓	✓	✓
Liberty LatchLoc		✓		✓		✓		✓	✓	✓	✓	✓
WoodSpring		✓	✓	✓	✓		✓			✓	✓	✓

CALL 800-642-6440 or VISIT www.harlequinfloors.com

For samples or information on Harlequin Floors complete range of vinyl and sprung floors.