

# AGSTGC Datsheet

# Merlin Timed Gas Controller



WEATHERPROOF COVER AVAILABLE

# **Technical Specification**

## **Product Overview**

The AGSTGC provides a timed supply of gas to outdoor units such as grills, heaters and decorative fire features.

110VAC or 24VAC/DC output to gas solenoid valves or an electrical power supply. Each controller has a selectable time out function built-in via internal dip switches, for 30min, 1hrs, 2hrs or 3hrs. When the timer has reached the owner's selected setting, the front LED will flash to warn user of the time out.

The AGSTGC is manufactured in a modern polycarbonate enclosure which provides protection from damage. The AGSTGC is designed to replace contractor constructed solutions for timed supply and panic shutdown, incorporating a crucial reset of the timed supply after a panic shutdown.

General	
Model:	AGS TGC – Timed Gas Controller
Size: (H x W x D)	5.95 x 4.37 x 1.97" (151 x 111 x 50mm)
Housing Material:	ABS PA765 (Flame Rating UL94 V-1)
Mounting:	Wall/Surface Mounted. Indoor use only – Outdoor using weatherproof cover.
Weatherproof Cover (Optional Part)	UV stabilized. 1lb. 5x5x5"
Weight:	11.2 oz (0.32g)
Visual Indicators:	LED. Gas On / Timeout / Emergency Stop
Audible Buzzer:	60dB @ 3.28ft (1m). Quiet conditions.
Buttons:	Multi-Function – Gas On / Reset Timer / Gas Off
Power Consumption:	1.2W Max
Power Input #1:	100-120V~ 50-60Hz
Power Input #2	24V AC or DC
Internal Fuse:	Anti-Surge 3.15A @ 250Vac
Relays	One Relay - 3A @ 110V~
Ingress Protection:	Not formally evaluated. IP4X Determined by inspection.
Operating:	-20 ~ 50°C / 14 ~ 122°F 20 ~ 95% RH (non-condensing)
Storage:	-25 ~ 50°C / -13~122F° up to 95% RH (non-condensing)
Typical Wiring	Min. 18AWG / 75°C min / Tinned copper.
Overvoltage Category:	II
Electrical Safety and	CE / UKCA / IEC BS EN 61010-1
Electromagnetic Compatibility	EN 61326-1: 2013 / FCC CFR 47 Parts 15, 107 & 109

Find out more

### American Gas Safety LLC

www.americangassafety.com

Head office: 6304 Benjamin Road, Suite 502, Tampa, FL 33634 Tel: (727) 608-4375 Email: info@americangassafety.com

