

SOLVLVNC

Datasheet

2-Way, Internally Piloted
 Normally Closed, 1/2" - 2"
 NPT, Potable Water



120VAC, 24VAC
 or 24VDC
 Power Input



UL Listed



Normally Closed
 Safety Shutoff



1/2" to 2" NPT
 Available For This
 Model
 Various Other Sizes
 Also Available

Standards



Product Overview

AGS water solenoid valves are normally closed (N/C) and constructed with a durable lead free brass body, two-way inlet and outlet ports.

Sizes Available

120VAC Models

Valve Size " (inch) NPT	AGS Part Number
1/2"	SOLVLVNC12
3/4"	SOLVLVNC34
1"	SOLVLVNC1
1+1/4"	SOLVLVNC114
1+1/2"	SOLVLVNC112
2"	SOLVLVNC2

24VDC & 24VAC Models

Valve Size " (inch) NPT	AGS Part Number
1/2"	SOLVLV12NC-24V**
3/4"	SOLVLV34NC-24V**
1"	SOLVLV1NC-24V**
1+1/4"	SOLVLV114NC-24V**
1+1/2"	SOLVLV112NC-24V**
2"	SOLVLV2NC-24V**

**Include 'DC' or 'AC' Voltage To Partcode

Electrical Specifications

Voltage	120VAC / 24VAC	Voltage	24VDC
Frequency Hz	50/60	Frequency Hz	DC
Power (VA)	20	Power (W)	17 W
Rating	Nema 4	Rating	Nema 4
Coil Type	D	Coil Type	D
Coil Class	F	Coil Class	F

Materials of Construction

Body	Lead Free Brass
Armature Tube	Stainless Steel 300
Fixed Core	Stainless Steel 400
Plunger	Stainless Steel 400
Spring	Stainless Steel 300
Shading Ring	Copper
Orifice	Lead Free Brass

Technical Specifications

120VAC Models

Pipe Size (Inch)	Orifice (Inch)	Flow Factor (CV)	Pressure (PSI)	Temp. Range	Voltage	VA Rating	External Dimensions Length x Width x Height (Inches)	Model	Connector Supplied	Medium Examples	Sealing Material
1/2"	1/2"	4.5	0.5-230	32-266°F	120VAC	20	2.59 x 1.89 x 4.21	SOLVLVNC12	Wire Connector	Potable Water	EPDM
3/4"	3/4"	7.6	0.5-230	32-266°F	120VAC	20	2.95 x 2.28 x 4.40	SOLVLVNC34	Wire Connector	Potable Water	EPDM
1"	1"	12	0.5-230	32-266°F	120VAC	20	3.78 x 2.76 x 5.16	SOLVLVNC1	Wire Connector	Potable Water	EPDM
1 1/4"	1 1/4"	22	0.5-230	32-266°F	120VAC	20	5.16 x 3.78 x 5.75	SOLVLVNC114	Wire Connector	Potable Water	EPDM
1 1/2"	1 1/2"	30	0.5-230	32-266°F	120VAC	20	5.16 x 3.78 x 5.75	SOLVLVNC112	Wire Connector	Potable Water	EPDM
2"	2"	48	0.5-230	32-266°F	120VAC	20	6.50 x 4.72 x 6.57	SOLVLVNC2	Wire Connector	Potable Water	EPDM

24VAC Models

Pipe Size (Inch)	Orifice (Inch)	Flow Factor (CV)	Pressure (PSI)	Temp. Range	Voltage	VA Rating	External Dimensions Length x Width x Height (Inches)	Model	Connector Supplied	Medium Examples	Sealing Material
1/2"	1/2"	4.5	0.5-190	32-266°F	24VAC	20	2.59 x 1.89 x 4.21	SOLVLVNC12-24VAC	Wire Connector	Potable Water	EPDM
3/4"	3/4"	7.6	0.5-190	32-266°F	24VAC	20	2.95 x 2.28 x 4.40	SOLVLVNC34-24VAC	Wire Connector	Potable Water	EPDM
1"	1"	12	0.5-190	32-266°F	24VAC	20	3.78 x 2.76 x 5.16	SOLVLVNC1-24VAC	Wire Connector	Potable Water	EPDM
1 1/4"	1 1/4"	22	0.5-115	32-266°F	24VAC	20	5.16 x 3.78 x 5.75	SOLVLVNC114-24VAC	Wire Connector	Potable Water	EPDM
1 1/2"	1 1/2"	30	0.5-115	32-266°F	24VAC	20	5.16 x 3.78 x 5.75	SOLVLVNC112-24VAC	Wire Connector	Potable Water	EPDM
2"	2"	48	0.5-115	32-266°F	24VAC	20	6.50 x 4.72 x 6.57	SOLVLVNC2-24VAC	Wire Connector	Potable Water	EPDM

24VDC Models

Pipe Size (Inch)	Orifice (Inch)	Flow Factor (CV)	Pressure (PSI)	Temp. Range	Voltage	(W) Rating	External Dimensions Length x Width x Height (Inches)	Model	Connector Supplied	Medium Examples	Sealing Material
1/2"	1/2"	4.5	0.5-190	32-266°F	24VDC	17	2.59 x 1.89 x 4.21	SOLVLVNC12-24VDC	Wire Connector	Potable Water	EPDM
3/4"	3/4"	7.6	0.5-190	32-266°F	24VDC	17	2.95 x 2.28 x 4.40	SOLVLVNC34-24VDC	Wire Connector	Potable Water	EPDM
1"	1"	12	0.5-190	32-266°F	24VDC	17	3.78 x 2.76 x 5.16	SOLVLVNC1-24VDC	Wire Connector	Potable Water	EPDM
1 1/4"	1 1/4"	22	0.5-115	32-266°F	24VDC	17	5.16 x 3.78 x 5.75	SOLVLVNC114-24VDC	Wire Connector	Potable Water	EPDM
1 1/2"	1 1/2"	30	0.5-115	32-266°F	24VDC	17	5.16 x 3.78 x 5.75	SOLVLVNC112-24VDC	Wire Connector	Potable Water	EPDM
2"	2"	48	0.5-115	32-266°F	24VDC	17	6.50 x 4.72 x 6.57	SOLVLVNC2-24VDC	Wire Connector	Potable Water	EPDM

Popular Applications

- Schools
- Laboratories
- Residential
- Hospitals
- Drinking Water Control

Find out more

American Gas Safety LLC

www.americangassafety.com

Head office:

6304 Benjamin Road, Suite 502, Tampa, FL 33634

Tel: (727) 608-4375

Email: info@americangassafety.com

