AeroLift 35

Ceiling-Recessed Projector Lift with a 35 lb. (16kg) Lifting Capacity



Specifications Please check all appropriate selections and attach room schedule with verified dimensions.

QUANTITY: AEROLIFT 35
VIDEO PROJECTOR LIFTS.
Maximum capacity 35 lbs. (including projector, projector bracket, closure and ceiling material attached to closure).
Electrically operated 110-120V, 60 Hz. 3-wire motor, instantly reversible, lifetime lubricated, with internal thermal overload protector and brake. UL approved motor. Designed to be ceiling recessed or surface mounted to fit within a standard

2" x 10" beam, 16" on center, ceiling joist pocket. Lift

to have scissor arm for stabilization. Factory set limit switches automatically stop travel at open and closed positions. Threeposition, 110-120V switch to stop or reverse cycle at

Maximum vertical drop to be 24½". Net weight 20 lbs. AeroLift 35 is approved to UL 2442 and CSA C22.2 No. 60065-03.

OPTIONS
OPTIONAL ENVIRONMENTAL AIR SPACE
HOUSING: Aluminum and steel, for use in

environmental air space. Choose from two sizes: [Small $(149/16" \times 237/8")$ Net weight 95½ lbs] and [Large $(23\%" \times 23\%")$ Net weight 139 lbs]. Includes trim ring for ceiling opening.

CEILING CLOSURE PANEL: Finished in white baked CEILING CLOSURE PANEL: Finished in write baked textured powder coat, shall descend smoothly with projector. Choose from two sizes: Choose from two sizes (trim edge to trim edge): [SMALL (155/8" x 25"); weight 7.5 lbs;] and [LARGE (25" x 25"); clasure & angle brackets weigh 10 lbs.

CEILING FINISH KIT: Finished white. Trims ceiling opening when required. Choose from two sizes: [SMALL] and [LARGE]. Consists of trim ring and closure panel.

CEILING ACCESS DOOR: provides ceiling access when unit is installed above hard ceiling and access to projector is not convenient.

OPTIONAL UNIVERSAL PROJECTOR MOUNT: Fits most projectors up to 26 lbs. Tilt, yaw and pan adjustment.

OPTIONAL VIDEO CONFERENCING CAMERA ADAPTER BRACKET:

Enables installation of a video conferencing camera in AeroLift 35. Available in two sizes (Dimensions Small 7½" x 9" x 7½" or Large 9" x 12" x 9"). Special brackets available for oversize or dual camera installation.

Please Note: The AeroLift 35 should be specified in conjunction with a Draper video format motorized screen. Specifications subject to change without notice.

AeroLift 35 is approved to UL 2442 and CSA C22.2 No. 60065-03. Downloadable 3-part specifications: available at <u>www.draperinc.com</u>

Please note: Dimensions of rollers, operators, and hardware at

Select Control Options:

Please Note: This Draper motorized lift comes with one 110V-120V AC 3-position wall switch (silver wall plate with black rock

Total number of 110-120V AC switches

(switches operate independently)

Substitute white switch(es) for silver wall plate with black rocker

Optional Lift Low Voltage Control Module

24 Volt 3-Button Switch How many switches?

☐ Radio Frequency Remote Control (only with 24V)

☐ Infrared Remote Control (only with 24V)

Optional Key Operated Switch

Power Supply Key Switch (On-off)

3-Position Key Control

3-Position Switch with Hinged Key-Locking Coverplate

Select Optional Accessories (drawings on pages 2 & 3)

Please Note: Available colors listed where applicable. AeroLift is always black.

Optional Ceiling Access Door:

Access above finished ceiling (recommended) Accepts Ceiling Tile

□ Optional Environmental Air Space Housing: □ Small □ Large (Optional Ceiling Closure Panel not included.)

Powder Coat Finish of Visible Trim:

White (Standard) ■ Black (Optional)

☐ Optional Ceiling Closure Panel: ☐ Small ☐ Large

(Pairs with Environmental Air Space Housing.)

Powder Coat Finish:

White (Standard)

☐ Black (Optional)

□ Optional Ceiling Finish Kit: □ Small □ Large

(Ceiling Closure Panel and Trim Kit used to finish ceiling opening when no

Environmental Air Space Housing is needed.)

Powder Coat Finish:

White (Standard) ■ Black (Optional)

Optional Universal Projector Mount (max. load 26 lbs).

Optional Video Conferencing Camera Adapter Bracket

Small (9" w. x 7½"h. x 7½" d.) Large (12" w. x 9" h. x 9" d.)

Custom for oversize or dual cameras



Projector can be installed as shown or turned 90° depending on projector size.

AeroLift 35 shown with optional closure.

Dimensions & Data	Small Closure	Large Closure
Height of lift in closed position ¹	4 ¹³ / ₁₆ "	413/16"
Maximum Overall lift dimensions (WxL)	12½" x 22¼"	12½" x 22¼"
Ceiling opening (with closure)	23½" x 14 ³ / ₈ "	23½" x 23½"
Optional Env. Air Space Housing (WxL) ²	23 ⁷ / ₈ " x 14 ⁹ / ₁₆ "	23 ⁷ / ₈ " x 23 ⁷ / ₈ "
Max. projector size (with closure) (WxL) ³	8¾" x 18"	20" x 20"
Max. down travel	24½"	24½"
Approx. travel time to lowest position	14 sec.	14 sec.
Total Capacity (lbs.) ⁴	35	35
Net weight of lift (lbs.) 5	20	20
Amperes	1.2	1.2

¹Not including projector, mount or closure.

²Maximum Env. Air Space Housing Height: 20⁵/₈". Min. Env. Air Space Housing Height: 12⁵/₈".

3 Maximum Available Projector/Bracket Height (with Env. Air Space Housing): 15%

Minimum Available Projector/Bracket Height (with Env. Air Space Housing): 73/4" Small Closure weighs 7.5 lbs. Large Closure & Angle Brackets weigh 10 lbs.

⁵Unit Only: Does not include projector, mount, Env. Air Space Housing or closure.

MIMDRAPER®
Drapar Inc. I. 411 C. Doorl Ct. Opingland, IN 47005

Draper, Inc. | 411 S. Pearl St. Spiceland, IN 47385 draperinc.com | 765.987.7999 | 800.238.7999 © 2020 All Rights Reserved | FORM: AeroLift35_Sub20


PROJECT:_			
			

ARCHITECT:


CONTRACTOR: SUPPLIER:

DATE: **REVISED:** AeroLift 35 page 2 of 4


Dimensions




Dimensions: AeroLift 35 with MPL Environmental Air Space and Closure




Dimensions - AeroLift 35 with Small Environmental Air Space and Closure



Ceiling Finish Trim Kit (includes Closure Panel - for use WITHOUT Environmental Air Space Housing)




Optional Universal Projector Mount



Optional Video Conferencing Camera Adapter


	Available Sizes:		
	Α	В	С
Small	71/2"	7½"	9"
Large	9"	9"	12"




AeroLift 35 page 4 of 4

Wiring Diagrams

Single Station Control



LVC-IV - Low Voltage Controller





PROJECT:	
ARCHITECT:	
CONTRACTOR:	
SUPPLIER:	
DATE:	REVISED: