

# SPEEDHIDE® EXTERIOR

EXTERIOR PAINT



**EXCELLENT ADHESION**  
**GOOD UV & WEATHERING RESISTANCE**  
**MILDEW RESISTANT ON THE DRY PAINT FILM**

## FEATURES & BENEFITS

- Excellent adhesion provides resistance to chipping, peeling, and blistering
- Application in temperatures as low as 35°F (2°C) extends the painting season
- Good UV and weathering resistance means the paint will hold up to tough outdoor elements

## CONFORMANCE STANDARDS

<50 g/L VOC compliant in all regulated areas nationwide. Meets Green Performance Standards: GPS-1 & GPS-2. Meets MPI Category: 10, 11, & 15

*Speedhide* Exterior Latex is a durable, 100% acrylic exterior paint designed for new and repaint applications where durability and ease of application are most important in both the commercial and multi-family markets. This less than 50 g/L VOC paint provides excellent flow and leveling, very good hide and coverage, and has excellent resistance to mildew growth on the paint film. This 100% acrylic workhorse formula also provides excellent adhesion and can be applied at temperatures as low as 35°F (2°C), extending your painting season. *Speedhide* Exterior Latex is recommended on wood, masonry, fiber cement, brick, aluminum siding, and ferrous metal.

PPG SPEEDHIDE EXTERIOR FORMULA FEATURES						
	HIDE	DIRT PICK-UP RESISTANCE	ADHESION	TOUCH-UP	LEVELING	SAG RESISTANCE
SPEEDHIDE	★★★★☆	★★★★☆	★★★★☆	★★★★★	★★★★☆	★★★★★
LEADING STORE COMPETITOR	★★★★☆	★★★☆☆	★★★★☆	★★★★★	★★★★☆	★★★★★

\*Results are from internal and external testing and may vary slightly.



# SPEEDHIDE® EXTERIOR

PINTURA PARA EXTERIORES

EXCELENTE ADHESIÓN

BUENA RESISTENCIA A LOS RAYOS UV Y A LA INTEMPERIE

RESISTENTE AL MOHO EN LA PELÍCULA DE PINTURA SECA

## CARACTERÍSTICAS Y BENEFICIOS

- La excelente adhesión proporciona resistencia al astillado, pelado y formación de ampollas
- La aplicación en temperaturas tan bajas como 2°C (35°F) extiende la temporada de pintura
- Una buena resistencia a los rayos UV y a la intemperie significa que la pintura resistirá a los elementos exteriores

## ESTÁNDARES DE CONFORMIDAD

<50 g/l Cumple con los COV en todas las áreas reguladas a nivel nacional. Cumple con los estándares de rendimiento ecológico: GPS-1 y GPS-2. Cumple con la Categoría MPI: 10 11, y 15

*Speedhide* Exterior Látex es una pintura duradera, 100% acrílica para exteriores, diseñada para aplicaciones nuevas y de repintado donde la durabilidad y la facilidad de aplicación son más importantes tanto en el mercado comercial como en el multifamiliar. Esta pintura de menos de 50 g/L VOC proporciona un excelente flujo y nivelación, muy buen ocultamiento y rendimiento, y tiene una excelente resistencia al crecimiento de moho en la película de pintura. Esta fórmula eficaz 100% acrílica también proporciona una excelente adhesión y se puede aplicar a temperaturas tan bajas como 2°C (35°F), lo que prolonga la temporada de pintura. *Speedhide* Exterior Látex se recomienda en madera, mampostería, fibrocemento, ladrillo, revestimiento de aluminio y metal ferroso.

### CARACTERÍSTICAS DE LA FÓRMULA SPEEDHIDE:

	OCULTAMIENTO	RESISTENCIA A LA ACUMULACIÓN DE SUCIEDAD	ADHESIÓN	RETOQUE	NIVELACIÓN	RESISTENCIA AL DESCUELGE
<i>SPEEDHIDE</i>	★★★★☆	★★★★☆	★★★★☆	★★★★★	★★★★☆	★★★★★
COMPETIDOR LÍDER EN TIENDAS	★★★★☆	★☆☆☆☆	★★★☆☆	★★★★★	★★★★☆	★★★★★

\*Los resultados son de pruebas internas y externas y pueden variar ligeramente

## AVAILABLE SHEENS BRILLOS DISPONIBLES

CODE CÓDIGO	BASE BASE	SIZES TAMAÑOS
<b>FLAT MATE</b>		
6-610XI	White Blanco	1s, 5s
6-650XI	White & Pastel Blanco y pastel	1s, 5s
6-651XI	Midtone Tono medio	1s, 5s
6-653XI	Ultra-Deep Ultra profundo	1s, 5s
<b>SATIN SATINADO</b>		
6-2045XI	White Blanco	1s, 5s
6-2110XI	White & Pastel Blanco y pastel	1s, 5s
6-2150XI	Midtone Tono medio	1s, 5s
6-2300XI	Ultra-Deep Ultra profundo	1s, 5s
<b>SEMI-GLOSS SEMIBRILLANTE</b>		
6-900XI	White Blanco	1s, 5s
6-901XI	White & Pastel Blanco y pastel	1s, 5s
6-902XI	Midtone Tono medio	1s, 5s
6-904XI	Ultra-Deep Ultra profundo	1s, 5s

Visit [ppgpaints.com](http://ppgpaints.com) for more information.

PPG Architectural Finishes, Inc. • 400 Bertha Lamme Drive • Cranberry Twp, PA 16066  
 Technical Service: 1-800-441-9695 • Architect/Specifier: 1-888-774-7732

© 2019 PPG Industries, Inc. All Rights Reserved. The PPG Logo is a registered trademark of PPG Industries Ohio, Inc.  
*Speedhide* is a registered trademark of PPG Architectural Finishes, Inc. ST466584

