ITEM: SURFACE MOUNT

MATERIAL: TYPE 316 STAINLESS STEEL.

FITTING TYPE: NON-ADJUSTABLE CABLE END FITTING

SWAGE TYPE: MACHINE HEX SWAGE AT FACTORY (1/8" & 3/16" SIZES

ALSO AVAILABLE IN CABLECRIMP HAND SWAGE STYLE FOR FIELD

FABRICATION)

POST TYPE: WOOD. METAL POSSIBLE BUT NOT RECOMMENDED.

(POSTS NOT INCLUDED).

FASTENING TO POST: ATTACH TO FACE OF END/TERMINATION POST OR WALL

USING TWO SCREWS OR BOLTS.

FASTENING AT ANGLES: MOUNTING FLANGE PIVOTS UP TO 130 DEGREES.

CABLE TENSIONING: NON-ADJUSTABLE FIXED END.

HARDWARE PAIRINGS: USUALLY PAIRED WITH SURFACE MOUNT TURNBUCKLE. MUST

ONLY BE PAIRED WITH A TENSION ADJUSTMENT FITTING

(NOT ANOTHER FIXED END).


SUPPLIER: FEENEY, INC.

2603 UNION STREET, OAKLAND, CA 94607

PH: 1-800/888-2418 FAX:

1-510/893-9484

E-MAIL: sales@feeneywire.com
WEB: www.cablerail.com



## SURFACE MOUNT, STAINLESS STEEL

PART#	MODEL#	SWAGE TYPE	CABLE SIZE	HOLE DIA. (EØ)	HOLE SPAN (H) †	FLANGE WIDTH (W)	LENGTH (L)	ATTACHMENT POST DRILL HOLE Ø
3281	125-FSM-T	MACHINE	1/8"	1/4"	1-3/8"	5/8"	2-1/8"	LAG OR TAP
3284	187-FSM-T	MACHINE	3/16"	1/4"	1-3/8"	5/8"	2-1/4"	LAG OR TAP
3337	250-FSM-T	MACHINE	1/4"	5/16"	1-1/2"	3/4"	3-1/4"	LAG OR TAP
*3333	CC125-FSM-T	CABLECRIMP	1/8"	1/4"	1-3/8"	5/8"	3"	LAG OR TAP
3334	CC187-FSM-T	CABLECRIMP	3/16"	1/4"	1-3/8"	5/8"	3"	LAG OR TAP

<sup>\* 3333</sup> IS SAME AS A #3334 BUT INCLUDES A CONVERSION INSERT SLEEVE FOR CRIMPING ONTO 1/8" CABLE

CableRail Reference Drawing:

SURFACE MOUNT

DATE: 05/15/13
PAGE: 1 of 1
REV: A (12/15/17) MRJ
BY: DSY
CHK: BWA



2603 Union St., Oakland, CA 94607 P: 800-888-2418 F: 510-893-9484 www.feeneyinc.com

<sup>†</sup> SINCE FLANGES ARE FORMED PIECES, ALLOW A TOLERANCE OF ±1/16" ON FLANGE HOLE SPAN DIMENSION (H).