ITEM: SLEEKLINE SURFACE MOUNT TURNBUCKLE

MATERIAL: TYPE 316 STAINLESS STEEL.

FITTING TYPE: ADJUSTABLE CABLE END TURNBUCKLE FOR ATTACHING &

TENSIONING LINES, SMOOTH, ATTRACTIVE APPEARANCE WITHOUT

ANY EXPOSED THREADS OR SWAGE ENDS.

SWAGE TYPE: CAN BE MACHINE SWAGED IN FACTORY BUT BEST SUITED

FOR FIELD ATTACHMENT USING CABLECRIMP HAND SWAGE

STYLE.

POST TYPE: WOOD. METAL POSSIBLE BUT NOT RECOMMENDED.

(POSTS NOT INCLUDED).

FASTENING TO POST: ATTACH TO FACE OF END/TERMINATION POST OR WALL

USING TWO SCREWS OR BOLTS.

FASTENING AT ANGLES: TURNBUCKLE MOUNTING FLANGE PIVOTS UP TO 130 DEGREES.

CABLE TENSIONING: ADJUST BY TURNING TUBULAR TURNBUCKLE BODY.

HARDWARE PAIRINGS: USUALLY PAIRED WITH FIXED SURFACE MOUNT OR ANOTHER SLEEKLINE

SURFACE MOUNT TURNBUCKLE. MAY ALSO USE ANY OTHER TENSION

ADJUSTMENT FITTING OR FIXED END.

SUPPLIER: FEENEY, INC.

## SLEEKLINE SURFACE MOUNT TURNBUCKLE, STAINLESS STEEL

INTERNAL THREAD

BL

ВØ

PART#	SWAGE TYPE	CABLE SIZE	HOLE DIA (EØ)	HOLE SPAN (H) †	FLANGE WIDTH (W)	SHAFT DIA (SØ)	BODY LENGTH (BL)	BODY DIA (BØ)	LENGTH CLOSED (OPEN) (L)
3309	MACHINE	1/8"	1/4"	1-3/8"	5/8"	1/4"	4-3/4"	1/2"	5-5/8" (7-1/4")
3310	MACHINE	3/16"	1/4"	1-3/8"	5/8"	1/4"	4-3/4"	1/2"	5-5/8" (7-1/4")
3311	CABLECRIMP	1/8"	1/4"	1-3/8"	5/8"	1/4"	4-3/4"	1/2"	5-5/8" (7-1/4")
3312	CABLECRIMP	3/16"	1/4"	1-3/8"	5/8"	1/4"	4-3/4"	1/2"	5-5/8" (7-1/4")

†SINCE FLANGES ARE FORMED PIECES, ALLOW A TOLERANCE OF ±1/16" ON FLANGE HOLE SPAN DIMENSION (H).

CableRail Reference Drawing:

## SLEEKLINE SURFACE MOUNT TURNBUCKLE

MOUNTING

FACE

DATE: 05/15/13
PAGE: 1 of 1
REV: B (12/08/17) MRJ
BY: DSY
CHK: BWA



2603 Union St., Oakland, CA 94607 P: 800-888-2418 F: 510-893-9484 www.feeneyinc.com