



ULTRALITE
TEMPERED
GLASS

rdm
GLASS SYSTEMS

INKAN
ULTRAIMAGE

INKAN
ARCHITECTURAL
METALS

INKAN
CONTRACT



DRAWINGS INDEX

Available Finishes	03	#4500 and #4600 Push/Pull Handles	44
Door Swing Ledger	04	#4700 Push/Pull Handles	45
100 Series Doors (Top & Bottom Rail)		Stainless Steel and Alum. Weather strip channel	46
- elevation	04	Glued on Weather strip Mohair	47
200 Series Doors (Top & Bottom Patch		Rail Weatherstrip Sections	48
Fittings) - elevation	05	510 Series Bottom Straight Slider	49
250 Series Doors (Combination Top Patch		Type 1 Sections (510 Slider)	50
Bottom Rail) - elevation	06	Type 2 Sections (510 Slider)	51
300 Series Doors (Fully Framed) elevation	07	#70 Bottom Casers & Tandem Rollers	52
100 Doors Sections	08	520 Series Top Hung Straight Slider	53
200 & 250 Doors Sections	09	Type 1 Sections (520 Slider)	54
300 Doors Sections	10	Type 2 Sections (520 Slider)	55
Inkan's Rails, Saddle and Threshold	11	Type 3 Sections (520 Slider)	56
Inkan's Styles, Headers and Channels.	12	Type 4 Sections (520 Slider)	57
Dorma BTS 80 Floor Closer	13	C-106-4 Top Nylon Roller & C-104 Track	
Dorma RTS 88 Over Head Concealed closer	14	C-995 Top Steel Rollers & C204 Track	58
Dorma #8062 Walking Beam Pivot	15	ST90 Top Track and Rollers HSW Roller	
#8062 Walking Beam Pivot Bracket	16	& Track	59
#156 & 156HD Top Pivot	17	Bottom Guide Pin and St/St Track	60
#355.5 & #7471K Bottom Pivot	18	Inkan 2Point and 1Point Interconnecting Pin	61
#8853 & #8856 Bottom Pivot	19	530 Series Top Hung Parallel Stacking Slider	62
Top and Bottom Pivot Patch #319.41 & #319.1		540 Series Top Hung 90° Staggered Stacking	
10mm and 12mm glass patch.	20	Slider	63
Top and Bottom Pivot Patch #319.41 & #319.1		Parallel & 90° Stacking Unit For 530 & 540	
19mm glass patch.	21	Slider System	64
InKan Corner Rail Patch	22	Sections (530 & 540 Slider)	65
#317.4 & #317.41 Tanson/Sidelite Pivot Patch		550 Series Bottom Parallel Staggered Stacking	
for 12mm and 15mm glass	23	Slider	66
#317.4 & Tanson/Sidelite Pivot Patch		560 Series Bottom 90° Staggered Stacking	
for 19mm glass	24	Slider	67
#319.35 and #593.1 Wall Pivot Patch	25	Stacking area Plan for 550 & 560 Series	68
#312.1 & #311.1 Offset Top & Bottom Door		Section for (550 & 560 Series Slider)	69
Patch for 12mm and 15mm glass	26	610 Series Bi-Fold doors	70
#312.1 & #311.1 Offset Top & Bottom Door		620 Series Accordion Doors	71
Patch for 19mm glass	27	610 & 620 Bi-Fold arms	72
#327.1 Transom/Sidelite Pivot Patch	28	Squash/Racquetball Court Typical Elevation	
#152 Transom Door Stop 12mm - 19mm glass	29	and Sections	73
#153 & #154 Transom/Sidelite Corner Patch		Shipping Dimensions and Weights for Squash	
Door Stop.	30	Racquetball courts	74
#16500 Patch Lock & #319.5 Patch Lock	31		
MS Locks	32		
MS Cylinders and Thumbturns	33		
#123 & 123.5 Door Stops	34		
Inkan Centre Lock and Keeper Housing	35		
Lock housing Wire Channel	36		
#201 Lock Housing	37		
#4000 and #4006 Push/Pulls Handles	38		
#4100 and #4200 Push/Pulls Handles	39		
#4300 Push/Pulls Handles	40		
#4400 Push/Pulls Handles (Ladder)	41		
#4400 Push/Pulls Handles (Full Height)	42		

NOTE:

These drawings were current on the date indicated. However, changes may occur at any time, and we suggest you check with InKan for newer versions.

MATERIALS and FINISHES

MATERIALS:

MILL FINISH ALUMINUM:

- Utility
- Anodizing Quality

STAINLESS STEEL

BRASS

BRONZE

INKAN'S ALUM. CHANNEL 1 1/2" X 1" AND 1" X 1" :

AVAILABLE IN 2 FINISHES:

- 1.: BRUSHED ALUM. STAINLESS STEEL FINISH.
- 2.: MIRROR ALUM. STAINLESS STEEL FINISH.

FINISHES:

ANODIZED:

- #17 Clear
- #26 Light Bronze
- #29 Black
- #40 Dark Bronze
- Special Orders also Available

PAINTED:

- Most Types of PAINT (EPOXY, DURANAR, etc.)
- COLOUR can be MATCHED to SAMPLE

POLISHING - SHEET:

- XL Buff Mirror Finish (bright)
- Blend 'S' Brushed Finish (satin)


POLISHING - ROD and BAR:

- Mirror Finish (bright)
- Brushed Finish (satin)

SWING LEGEND


CENTRE / OFFSET PIVOTING DOORS

Specify required option




BI-FOLD DOORS


Specify required option



100 SERIES TOP AND BOTTOM RAIL




200 SERIES TOP and BOTTOM PATCH FITTINGS





250 SERIES COMBINATION PATCH AND RAIL

SPECIAL NOTE:



Transoms over 30"
(762mm) in height
require Fin Support




300 SERIES FULL FRAMED DOORS




100 SERIES



200 & 250 SERIES




SECTION @ DOOR (250 SERIES)



SECTION @ DOOR (200 SERIES)

300 SERIES



InKan DOOR / SIDELITE RAILS, SADDLE AND THRESHOLDS SECTIONS

For FINISHES, see Page 02


DASHED OUTLINE indicates OPTIONAL CLADDING

SOLID OUTLINE indicates CLADDING ONLY


ADD 1/8" to RAIL OVERALL HEIGHT for CLADDING ALLOWANCE

ADD 1/8" to RAIL WIDTH for CLADDING ALLOWANCE


CLAD STILES are BUILT OUT 1/16" PROUD of RAIL FACE




4" RAIL for
1/2" GLASS




4" RAIL for
3/4" GLASS




4" RAIL DEEP
POCKET RAIL
for 1/2" GLASS




4" RAIL DEEP
SLIDING RAIL
for 1/2~3/4" GLASS




6" RAIL DEEP
1/2" OR 5/8" GLASS




NEW 6" RAIL
3/4" OR LAMINATED GLASS




COMPOSITE RAIL for
1/2" TO 7/8" GLASS
Clad Only (ABOVE 12" +)




12" RAIL for
1/2" & 5/8" GLASS




1/8" SADDLE




1/4" SADDLE



3/4" SADDLE



4" THRESHOLD
5", 6" and 7"
ALSO AVAILABLE



4" THRESHOLD




InKan DOOR / SIDELITE HEADERS, CHANNELS AND VERTICAL STILES

For FINISHES, see Page 02


DASHED OUTLINE indicates OPTIONAL CLADDING

SOLID OUTLINE indicates CLADDING ONLY


CLAD STILES are BUILT OUT 1/16" PROUD of RAIL FACE




1 1/8" STILE for
1/2" GLASS




2 1/2" STILE for
1/2" GLASS




4" STILE for
1/2" GLASS




CUSTOM STILE for
1/2" GLASS
Clad Only




2 1/2" BEVELED
STILE for
1/2" GLASS




4" BEVELED
STILE for
1/2" GLASS




GLAZING CHANNEL
1" X 1" X 1" X 1/8"




GLAZING CHANNEL
1 1/2" X 1" X 1 1/2" X 1/8"




2-PART HEADER
for 1/2" GLASS




2-PART HEADER
CLOSED




HEADER / JAMB TUBE
1 3/4" X 4 1/2"



HEADER / JAMB TUBE
1 3/4" X 1 3/4"




HEADER / JAMB TUBE
1 3/4" X 4"




HEADER / JAMB TUBE
2" X 6"

HEADER / JAMB TUBE
Other sizes available.



HEADER / JAMB TUBE
4" X 4"




HEADER / JAMB TUBE
4 1/2" X 4 1/2"

DORMA BTS 80 FLOOR CLOSER

TECHNICAL DETAILS

- HANDING - DOUBLE ACTING
- PIVOTING - 3/4" OFFSET, 1 1/2" OFFSET and CENTRE LINE
- HOLD OPEN - MULTI-POINT, ADJUSTABLE BETWEEN APPROXIMATELY 75° and 180°
- BACKCHECK - MECHANICAL at APPROXIMATELY 85° and 165°
- DUTY - SPRING SIZE 2 (std) 26 ft-lbs (380 N/m) : MEDIUM SPRING
 1 (opt) 11 ft-lbs (160 N/m) : LIGHT SPRING
 3 (opt) 39 ft-lbs (570 N/m) : HEAVY SPRING
- SPINDLES - FIELD INTERCHANGEABLE, 5/16" to 2 5/16" DOOR CLEARANCE
 and 3° OFFSET on SOME SIZES
- DOOR WEIGHT - UP TO 660 lbs (300 kg) in INTERIOR APPLICATION;
 54" WIDE (TOP and BOTTOM RAIL) CENTRE HUNG ONLY
- COVER PLATES - BRUSHED or MIRROR STAINLESS STEEL
 BRASS and BRONZE to SPECIAL ORDER




DORMA RTS 88 OVERHEAD CONCEALED CLOSER

TECHNICAL DETAILS


- HEADER - 1 3/4" x 4" ALUMINUM TUBE
- HANDING - DOUBLE ACTING
- PIVOTING - CENTRE LINE ONLY
- HOLD OPEN - SPECIFY: HOLD OPEN/ NO HOLD OPEN, 90°/105°
- DUTY - SPRING SIZE 3 (std): MEDIUM
 - 2 (opt): LIGHT
 - 4 (opt): HEAVY
- SPINDLE - 3/8" or 3/4" LONG
- DOOR WEIGHT - MAXIMUM 250 lbs (113 kg), DEPENDING on BOTTOM PIVOT
- DOOR SWING - 130° SWING ARC
- BACKCHECK - CUSHIONED STOP from APPROXIMATELY 85°.
 - IF ADJACENT STRUCTURES INTERFERE with MAXIMUM DEGREE of DOOR SWING, AUXILIARY DOOR STOP SHOULD BE INSTALLED.

EXTERIOR APPLICATION SURFACE APPLIED STOP REQUIRED.




8062 WALKING BEAM PIVOT

CENTRE PIVOTING DOORS
PIVOT HOUSED into ALUMINUM TUBE or CHANNEL
MAXIMUM WEIGHT of DOOR: 440 lbs (200 kg)
DOOR PORTION - #319.2 INSERT for TOP PATCH




DOOR PIVOT INSERT


CENTRE PIVOTING DOORS
PIVOT HOUSED into InKan DOOR RAIL



PIVOT BLOCK




PIVOT GUIDE




8062 WALKING BEAM PIVOT STEEL SUPPORT BRACKET

PIVOT HOUSED into ALUMINUM TUBE or CHANNEL
MAXIMUM WEIGHT of DOOR: 440 lbs (200 kg)
DOOR PORTION - #319.2 INSERT for TOP PATCH




8062 WALKING BEAM PIVOT MOUNTED IN HEADER




#156 TOP MANUAL PIVOT

- FRAME MOUNTED
- FOR CENTRE PIVOTING DOORS
- DOOR PORTION - #319.2 INSERT for TOP PATCH (#157)
- MAX. WEIGHT CAPACITY 170 lbs (77 kg)



#156HD STAINLESS STEEL TOP MANUAL PIVOT

- FRAME MOUNTED
- FOR CENTRE PIVOTING DOORS
- DOOR PORTION - #319.2 INSERT for TOP PATCH (#157)
- MAX. WEIGHT CAPACITY 275 lbs (120 kg)





#355.5 FLOOR BEARING PIVOT

- SURFACE APPLIED to FLOOR or THRESHOLD
- FOR USE with DOOR RAIL ARM (#7421) or #319.1 BOTTOM DOOR PATCH
- WEIGHT CAPACITY: 440 lbs (200 kg)



AVAILABLE IN 4 DIFFERENT HEIGHTS:

- 8mm - STANDARD
- 5mm - EXTENSION AVAILABLE
- 10mm - EXTENSION AVAILABLE
- 15mm - EXTENSION AVAILABLE



#7471K FLOOR BEARING PIVOT

- SURFACE APPLIED to FLOOR or THRESHOLD
- FOR USE with DOOR RAIL ARM (#7421) or #319.1 BOTTOM DOOR PATCH * ON PATCH DOORS BOTTOM GAP WILL BE 11/16"
- WEIGHT CAPACITY: 440 lbs (200 kg)




8853 BOTTOM PIVOT

FLOOR MOUNTED
CENTRE LINE PIVOTING
FOR USE with DOOR RAIL - 2 3/4" PIVOT POINT
END LOADING
1/4" ADJUSTMENT
WEIGHT CAPACITY: 200 lbs (91 kg)

AVAILABLE IN 3 DIFFERENT HEIGHTS:


#8853 - SHOWN STANDARD (1/4"-7/16" GAP (CHANNEL RAIL DEPTH 1 9/16")
#8852 - AVAILABLE ON REQUEST (3/8"-5/8" GAP (CHANNEL RAIL DEPTH 7/8")
#8855 - AVAILABLE ON REQUEST (3/16"-7/16" GAP (CHANNEL RAIL DEPTH 7/8")



8856 FLOOR PIVOT - THRESHOLD

25/32" Ø HOLE in THRESHOLD
CENTRE LINE PIVOTING
FOR USE with DOOR RAIL - 2 3/4" PIVOT POINT
END LOADING
1/4" ADJUSTMENT
WEIGHT CAPACITY: 200 lbs (91 kg)



#8856 - SHOWN STANDARD (3/16"-7/16" GAP (CHANNEL RAIL DEPTH 1 3/8")



TOP DOOR PATCH

#319.41 for DORMA 88 OVERHEAD CLOSER
#319.2 for #156 TOP PIVOT




PATCHES for 1/2" GLASS
ADAPTABLE for 3/8" and 5/8" GLASS



BOTTOM DOOR PATCH

#319.1 for DORMA 80 FLOOR CLOSER or
#355.5 FLOOR BEARING PIVOT

PATCHES for 1/2" GLASS
ADAPTABLE for 3/8" and 5/8" GLASS





TOP DOOR PATCH

#319.41 for DORMA 88 OVERHEAD CLOSER

#319.2 for #156 TOP PIVOT

PATCHES for 3/4" GLASS (SPECIAL ORDER)






BOTTOM DOOR PATCH

#319.1 for DORMA 80 FLOOR CLOSER or

#355.5 FLOOR BEARING PIVOT

PATCHES for 3/4" GLASS (SPECIAL ORDER)



INKAN RAIL PATCH



TOP AND BOTTOM RAIL PATCH.

4" HIGH X 12 3/4" LONG


PATCHES for 1/2", 5/8" & 3/4" GLASS

ANY TOP & BOTTOM PIVOT AVAILABLE FOR RAILS

AVAILABLE IN ANY FINISH.



BOTTOM PATCH SHOWN






TRANSOM /SIDELITE PIVOT PATCH

#317.4R - RIGHT HAND

#317.4L - LEFT HAND

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS



TRANSOM /SIDELITE PIVOT PATCH for FIN

#317.41R - RIGHT HAND




#317.41L - LEFT HAND

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS

3/4" GLASS to SPECIAL ORDER

FIN GLASS is 1/2" (min), 5/8" or 3/4"






TRANSOM /SIDELITE PIVOT PATCH

#317.4R - RIGHT HAND


#317.4L - LEFT HAND

PATCHES for 3/4" GLASS (SPECIAL ORDER)



TRANSOM /SIDELITE PIVOT PATCH FOR FIN

PATCHES for 3/4" GLASS (SPECIAL ORDER)




TRANSOM /WALL PIVOT PATCH

#319.35 PIVOT PATCH - WALL MOUNTED

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS

3/4" GLASS to SPECIAL ORDER




SIDELITE /FIN BRACKET

#593.1 BRACKET PATCH

MOUNTED to FRAME or PATCH BODY

SPECIFY GLASS THICKNESS







OFFSET TOP DOOR PATCH

#312.1R - RIGHT HANDED SINGLE ACTING

#312.1L - LEFT HANDED SINGLE ACTING

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS



OFFSET BOTTOM DOOR PATCH

#311.1R - RIGHT HANDED SINGLE ACTING





#311.1L - LEFT HANDED SINGLE ACTING

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS

3/4" GLASS to SPECIAL ORDER

SEE PG. 26




OFFSET TOP DOOR PATCH

#312.1R - RIGHT HANDED SINGLE ACTING

#312.1L - LEFT HANDED SINGLE ACTING

PATCHES for 3/4" GLASS (SPECIAL ORDER)




OFFSET BOTTOM DOOR PATCH

#311.1R - RIGHT HANDED SINGLE ACTING

#311.1L - LEFT HANDED SINGLE ACTING

PATCHES for 3/4" GLASS (SPECIAL ORDER)



TRANSOM/SIDELITE PIVOT PATCH - OFFSET


#327.1R - RIGHT HANDED SINGLE ACTING

#327.1L - LEFT HANDED SINGLE ACTING

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS


3/4" GLASS to SPECIAL ORDER



OFFSET ARM

CAN BE MOUNTED on ANY InKan RAIL

SPECIFY HANDING and PIVOT TYPE






TRANSOM DOOR STOP

#152 PATCH - SINGLE ACTING

PATCHES for 1/2" GLASS




ADAPTABLE for 3/8" and 5/8" GLASS



TRANSOM DOOR STOP

#152 PATCH - SINGLE ACTING

PATCH for 3/4" GLASS (SPECIAL ORDER)





TRANSOM /SIDELITE CORNER PATCH

#153 PATCH - DOUBLE ACTING

PATCHES for 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS

3/4" GLASS to SPECIAL ORDER





TRANSOM /SIDELITE DOOR STOP

#154 PATCH - SINGLE ACTING DOORS

PATCHES for 1/2" GLASS


ADAPTABLE for 3/8" and 5/8" GLASS

3/4" GLASS to SPECIAL ORDER



#16500 PATCH LOCK


PATCHES for 1/2" GLASS
ADAPTABLE for 3/8" and 5/8" GLASS
3/4" GLASS to SPECIAL ORDER



#319.5 PATCH LOCK


PROFILE CYLINDER - CANNOT be MASTER-KEYED to
NORTH AMERICAN BUILDING SYSTEMS

PATCHES for 1/2" GLASS
ADAPTABLE for 3/8" and 5/8" GLASS
3/4" GLASS to SPECIAL ORDER






MS LOCKS

5 TYPES OF LOCKS




AR 1830

for Bottom Rail locking
BOLT - 3/8" x 5/8" x 2 1/8" with 5/8" throw
AR 1833 FORK TONGUE LOCK is SIMILAR.
KEEPER AVAILABLE





AR 4711

HEAVY DUTY DEAD LATCH
for STILES and LOCK HOUSINGS
LATCH BOLT - 5/8"x 1" with 1/2" throw
HANDING REVERSIBLE
AUXILIARY BOLT - DEADLOCKS
LATCH BOLT when retracted





AR 1850

for Bottom Rail locking
BOLT -
5/8" x 1 3/8" x 2 7/8" with 1 3/8" throw
KEEPER AVAILABLE





AR 1861

for Bottom Rail locking
BOLT - 3/8" with 13/16" THROW.
TWO POINT LOCK - 3/8" with 1 1/8" throw
DUST PROOF KEEPER AVAILABLE



#777S

for Bottom Rail locking
BOLT - 5/8" with 11/16" THROW.
DUST PROOF KEEPER AVAILABLE



AR 4591

LATCH PADDLE DEVICE for AR 4711 LOCK.
PADDLE - EXTRUDED ALUMINUM
SATIN ANODIZED, DARK BRONZE or
BLACK HARD COLOUR
HANDING - PUSH LEFT (02); PUSH RIGHT (04);
PULL LEFT (01); PULL RIGHT (03).

MS LOCKS, CYLINDERS, AND THUMBTURNS


CYLINDER BACKSET - 31/32" or 1 1/8"

CYLINDER and THUMBTURN - 1 5/32"Ø MORTISE with MS CAM


AMERICAN STANDARD CYLINDER

STANDARD 1" LONG CYLINDERS

LONGER CYLINDERS AVAILABLE.



CYLINDER



THUMBTURN

InKan #123 DOOR STOP (DOUBLE DOOR)



MATERIAL: STAINLESS STEEL OR ALUMINUM

FINISH: BRUSHED (BLEND 'S') OR MIRROR FINISH IN STOCK.

FINISH: ANODIZED IN STOCK

SPECIAL ORDER ON ANODIZED FINISH:

BLACK, BRONZE K-40, BRONZE K-26, CHAMPAGNE,
STAINLESS STEEL, CLEAR, GOLD, GREEN, BLUE AND RED



InKan #123.5 DOOR STOP (SINGLE DOOR)


MATERIAL: STAINLESS STEEL OR ALUMINUM

FINISH: BRUSHED (BLEND 'S') OR MIRROR FINISH IN STOCK.

FINISH: ANODIZED IN STOCK


SPECIAL ORDER ON ANODIZED FINISH:

BLACK, BRONZE K-40, BRONZE K-26, CHAMPAGNE,
STAINLESS STEEL, CLEAR, GOLD, GREEN, BLUE AND RED




INKAN CENTRE HOUSING and KEEPER

HEAVY DUTY MORTISE LATCH LOCK,
LEVER HANDLE and KEEPER SET.
AVAILABLE FOR GLASS 1/2" TO 3/4" THK.



INKAN CENTRE HOUSING with ELECTRIC STRIKE KEEPER



HEAVY DUTY MORTISE LATCH LOCK,
LEVER HANDLE and KEEPER SET.
AVAILABLE FOR GLASS 1/2" TO 3/4" THK.



STAINLESS STEEL WIRE CHANNEL TO CONCEAL WIRES
TAMPER RESISTANT
STATIC STRENGTH 3,070 lbs. (FAIL SECURE)
DYNAMIC STRENGTH 350 ft-lbs. (FAIL SECURE)
FAIL SECURES (STANDARD)
DUAL VOLTAGE 12VDC or 24VDC CONTINUOUS DUTY

WIRE CHANNEL

AVAILABLE for 1/4" TO 3/4" GLASS
For FINISHES, see Page 02





CYLINDRICAL LOCK HOUSING and KEEPER

AVAILABLE with PASSAGE, PRIVACY, or OFFICE FUNCTIONS

For 1/2" GLASS

ADAPTABLE for 3/8" and 5/8" GLASS

AVAILABLE LEVER HANDLES



201 LOCK HOUSING
STANDARD LOCKSET with
2 3/4" BACKSET


205 KEEPER HOUSING

PUSH and PULL HANDLES (4000 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
HANDLE DIAMETER - $\varnothing 1"$
ROSETTE DIAMETER - 1 1/4"
MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
GLASS HOLE - 5/8" \varnothing
MINIMUM FIXTURE - 3/8"
MAXIMUM FIXTURE - 2 1/2" STILE
STOCK HANDLES - ALL MATERIALS

4012 SERIES - 12" O/A HANDLES IN STOCK
OTHER SIZES AVAILABLE ON ORDER.


IDENTIFICATION EXAMPLES: 4012 : distance 'a' = 12"
4027 3/4 : distance 'a' = 27 3/4"



BACK to BACK
MOUNTING



SECURITY FASTENER




(4012 SERIES)


PUSH and PULL HANDLES (4006 SERIES)

PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
HANDLE DIAMETER - $\varnothing 3/4"$
ROSETTE DIAMETER - 1 1/4"
MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
GLASS HOLE - 5/8" \varnothing
MINIMUM FIXTURE - 3/8"
MAXIMUM FIXTURE - 2 1/2" STILE
STOCK HANDLES - ALL MATERIALS


4006 SERIES - 6" O/A HANDLES IN STOCK



BACK to BACK
MOUNTING



SECURITY FASTENER




(4006 SERIES)

PUSH and PULL HANDLES (4100 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
HANDLE DIAMETER - $\varnothing 1"$
ROSETTE DIAMETER - 1 1/4"
MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
GLASS HOLE - 5/8" \varnothing
MINIMUM FIXTURE - 3/8"
MAXIMUM FIXTURE - 2 1/2" STILE
STOCK HANDLES - ALL MATERIALS

4112 SERIES - 12" O/A HANDLES IN STOCK
OTHER SIZES AVAILABLE ON ORDER.



IDENTIFICATION EXAMPLES: 4112 : distance 'a' = 12"
4127 3/4 : distance 'a' = 27 3/4"



BACK to BACK
MOUNTING



SECURITY FASTENER




(4112 SERIES)

PUSH and PULL HANDLES (4200 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
HANDLE DIAMETER - $\varnothing 1"$
ROSETTE DIAMETER - 1 1/4"
MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
GLASS HOLE - 5/8" \varnothing
MINIMUM FIXTURE - 3/8"
MAXIMUM FIXTURE - 2 1/2" STILE
STOCK HANDLES - ALL MATERIALS

4212 SERIES - 12" O/A HANDLES IN STOCK
OTHER SIZES AVAILABLE ON ORDER.


IDENTIFICATION EXAMPLES: 4212 : distance 'a' = 12"
4227 3/4 : distance 'a' = 27 3/4"



BACK to BACK
MOUNTING



SECURITY FASTENER




(4212 SERIES)

PUSH and PULL HANDLES (4300 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
 HANDLE DIAMETER - $\varnothing 1"$
 ROSETTE DIAMETER - 1 1/4"
 MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
 GLASS HOLE - 5/8" \varnothing
 MINIMUM FIXTURE - 3/8"
 MAXIMUM FIXTURE - 2 1/2" STILE
 STOCK HANDLES - ALL MATERIALS

4312 SERIES - 12" O/A HANDLES IN STOCK
 OTHER SIZES AVAILABLE ON ORDER.


IDENTIFICATION EXAMPLES: 4312 : distance 'a' = 12"
 4327 3/4 : distance 'a' = 27 3/4"



BACK to BACK
MOUNTING



SECURITY FASTENER



(4312 SERIES)



PUSH and PULL HANDLES

(4400 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
 HANDLE DIAMETER - $\varnothing 1 \frac{1}{4}$ "
 ROSETTE DIAMETER - $\varnothing 1 \frac{1}{4}$ " / STANDOFF - 2 LOCATIONS $1" \varnothing$
 MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
 GLASS HOLE - $\frac{3}{4}" \varnothing$
 MINIMUM FIXTURE - $\frac{3}{8}"$
 MAXIMUM FIXTURE - $2 \frac{1}{2}"$ STILE

ON GLASS MOUNTING APPLICATIONS
 ANY SIZES AVAILABLE UPON ORDER.
 OVER 60" SPAN BETWEEN STANDOFFS WILL REQUIRE A 3RD STANDOFF.

IDENTIFICATION EXAMPLES: 4424 : distance 'a' = 24"
 4472 : distance 'a' = 72"



SECURITY FASTENER



(4472 SERIES)



PUSH and PULL HANDLES

(4400 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
HANDLE DIAMETER - $\varnothing 1 \frac{1}{4}$ "
ROSETTE DIAMETER - $\varnothing 1 \frac{1}{4}$ " / STANDOFF - 2 LOCATIONS $1" \varnothing$
MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
GLASS HOLE - $\frac{3}{4}" \varnothing$
MINIMUM FIXTURE - $\frac{3}{8}"$
MAXIMUM FIXTURE - $2 \frac{1}{2}"$ STILE

RAIL AND GLASS MOUNTING APPLICATIONS (FULL HEIGHT PUSH/PULLS)
ANY SIZES AVAILABLE UPON ORDER.
OVER 60" SPAN BETWEEN STANDOFFS WILL REQUIRE A 3RD STANDOFF.

IDENTIFICATION EXAMPLES: 4495 $\frac{3}{4}$: distance 'a' = $95 \frac{3}{4}"$



SECURITY FASTENER




(4495 $\frac{3}{4}$ SERIES)

PUSH and PULL HANDLES (4500 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
 HANDLE DIAMETER - $\varnothing 1"$
 ROSETTE DIAMETER - 1 1/4"
 MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
 GLASS HOLE - 5/8" \varnothing
 MINIMUM FIXTURE - 3/8"
 MAXIMUM FIXTURE - 2 1/2" STILE
 STOCK HANDLES - ALL MATERIALS

CUSTOM ORDER HANDLE AVAILABLE


IDENTIFICATION EXAMPLES: 4512 : distance 'a' = 12"
 4527 3/4 : distance 'a' = 27 3/4"



BACK to BACK
MOUNTING




SECURITY FASTENER




(4500 SERIES)

PUSH and PULL HANDLES (4600 SERIES)


PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE
 HANDLE DIAMETER - $\varnothing 1"$
 ROSETTE DIAMETER - 1 1/4"
 MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM
 GLASS HOLE - 5/8" \varnothing
 MINIMUM FIXTURE - 3/8"
 MAXIMUM FIXTURE - 2 1/2" STILE
 STOCK HANDLES - ALL MATERIALS
 CUSTOM ORDER HANDLE AVAILABLE



SECURITY FASTENER



BACK to BACK
MOUNTING



4600 COMBINATION
 (4000 + 4100)
 Specify both
 'A' & 'B' dimensions

PUSH and PULL HANDLES (4700 SERIES)

PUSH /PULLS can be MOUNTED BACK to BACK or SINGLE SIDE

HANDLE DIAMETER - $\varnothing 1"$

ROSETTE DIAMETER - 1 1/4"

MATERIAL - BRASS, BRONZE, STAINLESS STEEL and ALUMINUM


GLASS HOLE - 5/8" \varnothing

MINIMUM FIXTURE - 3/8"

MAXIMUM FIXTURE - 2 1/2" STILE

STOCK HANDLES - ALL MATERIALS

CUSTOM ORDER HANDLE AVAILABLE



STANDARD InKan WEATHER-STRIP


for 3/8", 1/2", 5/8" and 3/4" GLASS

MATERIAL: BRASS, BRONZE OR STAINLESS STEEL.

FINISH: BRUSHED (BLEND 'S') OR MIRROR FINISH.

INSTOCK STAINLESS STEEL FOR 1/2", 5/8" & 3/4"

SLIDE IN MOHAIR PILE.



STANDARD InKan WEATHER-STRIP

for 3/8" & 1/2" and 3/4" to 15/16" GLASS


MATERIAL: ALUMINUM

FINISH: ANODIZED. - IN STOCK

SPECIAL ORDER:

BLACK, BRONZE K-40, BRONZE K-26, CHAMPAGNE,
STAINLESS STEEL, CLEAR, GOLD, GREEN, BLUE AND RED

SLIDE IN MOHAIR PILE.



InKan Hat pull handle (1/16" (16ga) THK. Formed)


for 1/2", 5/8" and 3/4" GLASS

MATERIAL: BRASS, BRONZE OR STAINLESS STEEL.


FINISH: BRUSHED (BLEND 'S') OR MIRROR FINISH.

PULL TO BE SILICONE TO GLASS

PLAN VIEW



ELEVATION VIEW



Hat Pull shown for 5/8" THK. Glass




Hardware Line for Tempered Glass Doors




STANDARD InKan WEATHER-STRIP - SELF ADHESIVE (GLUE ON)

for 3/8", 1/2", 5/8" AND 3/4" GLASS




STANDARD InKan WEATHER-STRIP - RAIL SURFACE APPLIED

ANY FINISH AVAILABLE
SEE PG. 2



STANDARD InKan WEATHER-STRIP - IN RAIL WEATHER-STRIP



510 SERIES BOTTOM STRAIGHT SLIDER

* AVAILABLE IN 2 TYPES OF BOTTOM
ROLLING TRACK CONFIGURATIONS.

510-1 SERIES TANDEM ROLLER - NOT TO EXCEED 113 Kg (250 lbs.)

Roller detail shown on Page 50

510-2 SERIES BOTTOM #70 CASTER - NOT TO EXCEED 181 Kg (400 lbs.)

Caster detail shown on Page 50

PANEL RAIL OPTIONS:

4" or 6" EXTRUDED ALUMINUM RAIL
or VARIABLE HEIGHT COMPOSITE
ALUMINUM RAIL (clad only)

ALUMINUM FINISH:

See Page 02

EXTRA FEATURES:

DOUBLE TRACK STYLE:


CYLINDER on OUTSIDE PANEL ONLY

THUMBTURN on INSIDE PANEL ONLY

INLINE TRACK STYLE:


CYLINDER on END PANELS

THUMBTURN on ALL PANELS with LOCKS




510 SERIES

TYPE 1



510 SERIES

TYPE 2




#70 BOTTOM CASTER

For 510, 550 & 560 SLIDER SYSTEMS

MAXIMUM PANEL WEIGHT: 181 Kg (400 lbs.)

Top guide pins must align with caster for stacking.




TANDEM ROLLER

For 510 SERIES SYSTEMS

MAXIMUM PANEL WEIGHT: 113 Kg (250 lbs)

ROLLER LOCATED 2 1/2" from RAIL ENDCAP.

Adjustment screw accessed by removing endcap



520 SERIES TOP HUNG STRAIGHT SLIDER

* AVAILABLE IN 4 TYPES OF TOP HUNG
ROILING TRACK CONFIGURATIONS.

520-1 SERIES C-104 TRACK/C-106-4 NYLON ROLLERS - NOT TO EXCEED 85 Kg (175 lbs.)

Roller detail shown on Page 56

520-2 SERIES C-204 TRACK/C-995 ROLLERS - NOT TO EXCEED 182 Kg (400 lbs.)

Caster detail shown on Page 56

520-3 SERIES HSW SYSTEM - NOT TO EXCEED 150 Kg (330 lbs.)

Caster detail shown on Page 57

520-4 SERIES ST90 SYSTEM - NOT TO EXCEED 273 Kg (600 lbs.)

Caster detail shown on Page 57 (FOR MAINTENANCE REPAIRS ONLY)

PANEL RAIL OPTIONS:

4" or 6" EXTRUDED ALUMINUM RAIL
or VARIABLE HEIGHT COMPOSITE
ALUMINUM RAIL (clad only)

ALUMINUM FINISH:

See Page 02

EXTRA FEATURES:

DOUBLE TRACK STYLE:

CYLINDER on OUTSIDE PANEL ONLY

THUMBTURN on INSIDE PANEL ONLY



INLINE TRACK STYLE:

CYLINDER on END PANELS

THUMBTURN on ALL PANELS WITH LOCKS

#331 PATCH can be INSTALLED INTO an INKAN


RAIL. EXPOSED FASTENERS MAY be PRESENT.



520 SERIES

TYPE 1


520-1 SERIES C-104 TRACK/C-106-4 NYLON ROLLERS - NOT TO EXCEED 85 Kg (175 lbs.)



520 SERIES

TYPE 2


520-2 SERIES C-204 TRACK/C-995 ROLLERS - NOT TO EXCEED 182 Kg (400 lbs.)



520 SERIES

TYPE 3


520-3 SERIES HSW SYSTEM - NOT TO EXCEED 150 Kg (330 lbs.)



520 SERIES

TYPE 4


520-4 SERIES ST90 SYSTEM - NOT TO EXCEED 273 Kg (600 lbs.)
(FOR MAINTENANCE REPAIRS ONLY)



C-106-4 TOP NYLON ROLLER AND C-104 TRACK

PANEL WEIGHT NOT to EXCEED 80 Kg (175 lbs.)
ROLLER LOCATED at PANEL QUARTER POINTS.


For 520 SERIES SYSTEM



C-995 TOP STEEL ROLLER AND C-204 TRACK

PANEL WEIGHT NOT to EXCEED 182 Kg (400 lbs.)
ROLLER LOCATED at PANEL QUARTER POINTS.

For 520 SERIES SYSTEM





ST90 TOP TRACK and ROLLER

For 520 SLIDERS

PANEL WEIGHT NOT TO EXCEED 273 Kg (600 lbs.)
(FOR MAINTENANCE REPAIRS ONLY)

ADEQUATE STRUCTURAL SUPPORT REQUIRED.
Adequacy to be determined by project architect
and/or structural engineer.




HSW TOP TRACK and ROLLER

For 520, 530 & 540 SLIDERS

PANEL WEIGHT NOT TO EXCEED 150 Kg (330 lbs.)



ADEQUATE STRUCTURAL SUPPORT REQUIRED.
Adequacy to be determined by project architect
and/or structural engineer.



BOTTOM GUIDE PIN and TRACK


For 520, 530 and 540 SLIDERS

FLOOR TRACK and GUIDE PIN on 520, 530 and 540 SERIES SYSTEMS are OPTIONAL. AR1861 pin lock and keeper can be used in their place to lock each panel. See Page 33.




InKan 2 Point Interconnecting pin

used with HSW sliding system (SERIES 520, 530 & 540 SLIDERS)



InKan 1 Point Interconnecting pin

used with HSW sliding system (SERIES 520, 530 & 540 SLIDERS)



530 SERIES

TOP HUNG PARALLEL STAGGERED STACKING SLIDER


ADEQUATE STRUCTURAL SUPPORT REQUIRED.
Adequacy to be determined by project architect
and/or structural engineer.

PANEL RAIL OPTIONS:


4" or 6" EXTRUDED ALUMINUM RAIL
or TOP PATCH SYSTEM (#331)
ALUMINUM RAIL (clad only)

* AVAILABLE IN 1 TYPE OF TOP HUNG
ROILING TRACK CONFIGURATIONS.

NOT TO EXCEED 150 Kg (330 lbs.)




AR1830 MODIFIED LOCK with
CYLINDERS OUTSIDE - See Page 33



AR1830 MODIFIED LOCK with
CYLINDERS OUTSIDE - See Page 33

STACKING ROOM with DOOR
BY OTHERS



EXTRA FEATURES:

30" EGRESS DOOR (54" wide panel min.)
FLOOR GUIDE FIN OPTIONAL



540 SERIES

TOP HUNG 90° STAGGERED STACKING SLIDER


ADEQUATE STRUCTURAL SUPPORT REQUIRED.
Adequacy to be determined by project architect
and/or structural engineer.

PANEL RAIL OPTIONS:


4" or 6" EXTRUDED ALUMINUM RAIL
or TOP PATCH SYSTEM (#331)
ALUMINUM RAIL (clad only)

* AVAILABLE IN 1 TYPE OF TOP HUNG
ROLLING TRACK CONFIGURATIONS.


NOT TO EXCEED 150 Kg (330 lbs.)



AR1830 MODIFIED LOCK with
CYLINDERS OUTSIDE - See Page 33



AR1830 MODIFIED LOCK with
CYLINDERS OUTSIDE - See Page 33




STACKING ROOM with DOOR
BY OTHERS

EXTRA FEATURES:

30" EGRESS DOOR (54" wide panel min.)
FLOOR GUIDE PIN OPTIONAL


PARALLEL STACKING UNIT

For 530 SLIDER SYSTEM




90° STACKING UNIT

For 540 SLIDER SYSTEM




530 & 540 SERIES

HSW TOP HANG SYSTEM - NOT TO EXCEED 150 Kg (330 lbs.)



2nd OPTION (HEAD DETAIL)



550 SERIES

BOTTOM PARALLEL STAGGERED STACKING SLIDER

PANEL RAIL OPTIONS:

4" or 6" EXTRUDED ALUMINUM RAIL
or VARIABLE HEIGHT COMPOSITE
ALUMINUM RAIL (clad only)



FINISHES:

See Page 02

* AVAILABLE IN 1 TYPE OF BOTTOM
ROILING TRACK CONFIGURATIONS.

NOT TO EXCEED 181 Kg (400 lbs.)

STACKING ROOM with DOOR
BY OTHERS



AR1861 LOCK with CYLINDERS
OUTSIDE. See Page 33

PARALLEL STAGGERED STACK

560 SERIES

BOTTOM 90° STAGGERED STACKING SLIDER

PANEL RAIL OPTIONS:

4" or 6" EXTRUDED ALUMINUM RAIL
or VARIABLE HEIGHT COMPOSITE
ALUMINUM RAIL (clad only)



FINISHES:

See Page 02

* AVAILABLE IN 1 TYPE OF BOTTOM
ROILING TRACK CONFIGURATIONS.

NOT TO EXCEED 181 Kg (400 lbs.)


STACKING ROOM with DOOR
BY OTHERS



AR1861 LOCK with CYLINDERS
OUTSIDE. See Page 33


PARALLEL STACKING UNIT

For 550 SLIDER SYSTEM




90° STACKING UNIT

For 560 SLIDER SYSTEM



550 & 560 SERIES

BOTTOM SYSTEM #70 - NOT TO EXCEED 181 Kg (400 lbs.)



610 SERIES

BI-FOLD DOOR

BI-FOLD DOORS:

EACH DOOR CONSISTS of TWO PANELS


- * MAXIMUM PANEL WIDTH: 32" (813mm)
- * MINIMUM PANEL WIDTH: 24" (610mm)
- * MAXIMUM PANEL HEIGHT: 84" (2134mm)

Bi-fold arms can be mounted in rails or patch fittings - see Page 06.

IMPORTANT NOTE:

FLOOR UNDER DOOR SWING MUST BE HORIZONTAL TO PREVENT CANTILEVERED PANELS FROM MAKING CONTACT.
Standard bottom clearance is 1/2" (12.7mm)

* Please contact us for advice on your requirements for CUSTOM DOORS exceeding these sizes.



620 SERIES ACCORDION DOOR

ACCORDION DOORS:

EACH DOOR CONSISTS of MORE THAN TWO PANELS

* MAXIMUM WIDTH for EACH PANEL: 36" (914mm)

ALL PANELS TO BE OF EQUAL WIDTH


* MAXIMUM PANEL HEIGHT: 96" (2438mm)

IMPORTANT NOTE:

FLOOR UNDER DOOR SWING MUST BE HORIZONTAL TO PREVENT CANTILEVERED PANELS FROM MAKING CONTACT.

Standard bottom clearance is 1/2" (12.7mm)



* Please contact us for advice on your requirements for CUSTOM DOORS exceeding these sizes.




BI-FOLD ARMS

For 610 SERIES BI-FOLD DOORS and
620 SERIES ACCORDION DOORS.



Arms are single acting only; can be
used with arms mounted into
rail section or patch.



PATCH FITTINGS



RAIL



SQUASH / RACQUETBALL COURT

All HARDWARE is in NYLATRON GREY NYLON.

FIN ANGLES, WALL ANGLES, and CHANNEL are in CLEAR ANODIZED FINISH.


GLASS is 1/2" CLEAR TEMPERED with OPTIONAL VERTICAL LINES along the bottom.

PLAYING SIDE has EXPOSED COUNTERSUNK FASTENERS for a FLUSH PLAYING SURFACE.

TEN BACK/SIDE WALL MODELS to choose from.

CUSTOM CONFIGURATIONS are AVAILABLE.

See PAGE 301 for
SHIPPING DIMENSIONS
and WEIGHTS



SQUASH / RACQUETBALL COURT

SHIPPING SIZES and APPROXIMATE WEIGHTS

MODEL	DESCRIPTION	WALL OPENING SIZE width x height	Approx. SHIPPING WEIGHT
AS-2P	American Squash - 2 Panels	222" x 78" 5639 x 1981 mm	1000 lbs 454 kg
AS-2PNF	American Squash - 2 Panels No Fins	222" x 78" 5639 x 1981 mm	875 lbs 397 kg
AS-4P	American Squash - 4 Panels	222" x 78" 5639 x 1981 mm	1050 lbs 476 kg
RB-2PNF	Racquetball - 2 Panels No Fins	240" x 84" 6096 x 2134 mm	1000 lbs 454 kg
RB-STD	Racquetball - Standard	240" x 144" 6096 x 3658 mm	1925 lbs 873 kg
RB-FHBW	Racquetball - Full Height Backwall	240" x 240" 6096 x 6096 mm	3100 lbs 1406 kg
RB-FHSW	Racquetball - Full Height Sidewall	480" x 240" 12192 x 6096 mm	6000 lbs 2722 kg
IS-2P	International Squash - 2 Panels	252" x 84" 6401 x 2134 mm	1150 lbs 522 kg
IS-2PNF	International Squash - 2 Panels No Fins	252" x 84" 6401 x 2134 mm	1000 lbs 454 kg
IS-4P	International Squash - 4 Panels	252" x 84" 6401 x 2134 mm	1225 lbs 556 kg
GDAF	Glass Door and Frame - Rough Stud Opening -	30" x 71 1/2" 762 x 1816 mm 33 1/8" x 75 1/2" 841.4 x 1918 mm	150 lbs 68 kg

NOTE: CUSTOM CONFIGURATIONS may include the
1997 standard for INTERNATIONAL DOUBLES
SQUASH with a court width of 300" (7620 mm)