

**Access**<sup>®</sup>  
*Products Inc.*

**eON**<sup>®</sup>  
**TILE**




## Designed for flexibility Engineered to last

Eon<sup>®</sup> Tile is a durable and flexible tactile indicator chosen first by professionals who design and construct the finest commercial, institutional and public environments.

Eon<sup>®</sup> Tile is state of the art polymers compounded together to create category leading quality and a contemporary look and finish. Suitable for a variety of applications such as airport concourses, railway stations, shopping centers, department stores, supermarkets, hospitals, swimming pools, schools, banks, community centers or most any high traffic environment. Eon<sup>®</sup> Tile's line of products offer attention indicators (truncated domes) for warning and tactile direction indicators for way finding. Eon<sup>®</sup> Tile is part of the newest generation of excellence in warning surfaces from Access Products Inc.

### COMPLIANCE

Access Products Inc. is in full compliance with American Disability Act Accessibility Codes. The full product range of Access Products tactile walking surface indicators meet the most recent federal and state building codes. Access Products Inc. is your one stop source for all tactile systems for internal and external applications. Only Access Products provide a complete range of products designed for safety, convenience and code compliance.




### PRODUCT FEATURES



- Made from premium long lasting polymers
- Flexible tiles will form to curved surfaces
- Flexible tiles become stable once bound to most surfaces
- Easily worked and shaped
- Appropriate for both initial installation, and surface retrofit
- UV resistant for color stability and ensures optimal visual surface contrast
- Conforms to contrast requirements (based on adjacent surfaces)
- 5 year manufacturer's warranty




**Tactile Attention Indicator with Truncated Domes**



**Tactile Direction Indicator with Guidance Bars**




**ELEVATION VIEW**



**ELEVATION VIEW**

Available in .012 or 0.19 inches thicknesses

## STANDARD COLORS



## TILE SPECIFICATIONS

Test	Description	Requirements
Antimicrobial Test	ASTM E2180	Pass
Fungi Test	ASTM G21	Pass
Tensile Strength	ASTM D412	0.17 MPa
Tensile Elongation	ASTM D412	700%
Tensile Stress	ASTM D412	6.9 MPa
Hardness (Shore A)	ASTM 2240	>85
Shrinkage	ASTM D955	0.9-1.5%
Melt Temperature		190-210° C
Moisture Content		0.05%

## APPLICATIONS

Tactile Attention Indicator <b>Truncated Domes</b>	<ul style="list-style-type: none"> <li>An unprotected drop off edge such as a transit platform.</li> <li>The unprotected edges of a reflecting pool.</li> <li>An entry into a vehicular route or area where no curbs or other elements separate it from a pedestrian route such as curb ramps, wheel chair ramps, top of stairs/escalators and blended transitions.</li> </ul>
Tactile Direction Indicator <b>Guidance Bars</b>	<ul style="list-style-type: none"> <li>Located in large open floor in large open floor areas, such as shopping malls or transportation terminals, to facilitate wayfinding by indicating the primary routes of travel.</li> <li>The indicated routes should lead from the entrance to major destinations, such as an information kiosk, registration desk, stairway, elevator, escalators, or to store or service doors.</li> </ul>